

QUOTATION

Penn Care Inc.

Penn Care
1317 North Rd
Niles, OH 44446
330-544-0777
330-544-0022
sales@penncare.net

Sales Rep:

Terms:

Drawing #:

Est. Delivery Date: / /

Customer PO #:

Penalty:

Customer #:

QPF #:

Exp. Date: 03/01/2015

Create Date: 01/30/2015

Rev. Date: / /

Quote No: 10184-0001

01/30/2015

Page 1

PART NO	S	DESCRIPTION	QTY	ID
== Express 2015 Type I / 144" Module - 15.000 11/06/14 ==			1	BI
00-01-0123	<	TYPE I - AMBULANCE - EXPRESS I - 68" INTERIOR HEADROOM	1	BI
		SHOP NOTE: 2015 EXPRESS I - 144" MODULE		
CHASSIS PACKAGES			1	BI
10-01-0117	<	CHASSIS - FORD F-350 CHASSIS, 165" WB 4 x 2 DRW	1	BI
		SHOP NOTE: 2015		
20-10-0099		FUEL TANK - FULL UPON FACTORY RELEASE	1	BI
20-10-0104	<	AIR SUSPENSION - KELDERMAN	1	BI
		SHOP NOTE: Air Ride System - (Kelderman)		
20-10-0206		BATTERY - TWO SYSTEM - F SERIES CHASSIS	1	BI
20-10-0603		ENGINE BLOCK HEATER - OEM PLUG	1	BI
20-20-0115	<	FLOOR CONSOLE - ANGLED FRONT - RECESS STORAGE- ABS	1	BI
		SHOP NOTE: A black vacuum-formed ABS center floor console with angled front, recessed storage well and two (2) drink holders shall be installed between the cab seats.		
20-20-0251		HEAT SHIELDS	1	BI
20-20-0277		HIGH IDLE SYSTEM, AUTOMATIC	1	BI
20-30-0202		MIRRORS, EXTERIOR OEM MANUAL TELESCOPING W/REMOTE & HEAT	1	BI
20-30-0261	<	OEM AUTO-LOCK DISABLED (cab & module doors do not auto lock or unlock)	1	BI
		SHOP NOTE: The OEM auto-lock feature will be disabled.		
20-30-0806		RUNNING BOARDS - STAR PUNCHED DIAMOND PLATE	1	BI

PART NO	S	DESCRIPTION	QTY	ID
20-40-0206		WHEEL SIMULATORS, STAINLESS STEEL WITH VALVE STEM EXTENSIONS	1	BI
30-06-0003		ELECTRICAL SYSTEM - WELDON V-MUX, MICRO PROCESSOR BASED	1	BI
30-06-0010		VISTA IV MCC - PUSH BUTTON	1	BI
30-06-0015		VISTA IV ACP - PUSH BUTTON	1	BI
30-06-0026		WARNING DISPLAY - MULTIPLEX ELECTRICAL SYSTEM	1	BI
30-06-0050		DAYTIME RUNNING LAMPS - MULTIPLEX ELECTRICAL SYSTEM	1	BI
30-06-0076		MASTER CONTROL CONSOLE (MCC) - MULTIPLEX ELECTRICAL SYSTEM	1	BI
30-06-0101		ATTENDANT CONTROL PANEL (ACP) - MULTIPLEX ELECTRICAL	1	BI
30-06-0126		ELECTRICAL COMPARTMENT (PDQ) - MULTIPLEX ELECTRICAL SYSTEM	1	BI
30-06-0150		SPARE CIRCUIT - MULTIPLEX ELECTRICAL SYSTEM	1	BI
30-06-0175		WIRING HARNESS CONNECTORS - MULTIPLEX ELECTRICAL SYSTEM	1	BI
30-06-0200		RADIO TIE-IN POINTS - MULTIPLEX ELECTRICAL SYSTEM	1	BI
30-06-0225		EMERGENCY MASTER SWITCH - MULTIPLEX ELECTRICAL SYSTEM	1	BI
30-06-0250		CONTROL PANEL SWITCHES - MULTIPLEX ELECTRICAL SYSTEM	1	BI
30-06-0275		MODULE POWER SWITCH - MULTIPLEX ELECTRICAL SYSTEM	1	BI
30-06-0285		MODULE DISCONNECT - MULTIPLEX ELECTRICAL SYSTEM	1	BI
30-06-0300		VOLTMETER - MULTIPLEX ELECTRICAL SYSTEM	1	BI
30-06-0325		FLASHER - MULTIPLEX ELECTRICAL SYSTEM	1	BI
30-06-0350		FLASHING HEADLIGHTS - MULTIPLEX ELECTRICAL SYSTEM	1	BI
30-06-0375		PARK OVERRIDE - MULTIPLEX ELECTRICAL SYSTEM	1	BI
30-06-0400		LOAD MANAGER-SEQUENTIAL SWITCHING SYSTEM - MULTIPLEX ELECTRIC	1	BI
30-06-0425		WARNING LIGHTS SWITCH - MULTIPLEX ELECTRICAL SYSTEM	1	BI
30-06-0450		FRONT CLEAR DISABLE SWITCH - MULTIPLEX ELECTRICAL SYSTEM	1	BI
30-06-0475		CURBSIDE SCENE LIGHTS "ON" WITH CURBSIDE DOOR - MULTIPLEX EL	1	BI
30-06-0500		REAR SCENE LIGHTS "ON" WITH REAR DOORS OPEN - MULTIPLEX ELEC	1	BI
30-06-0525		DISABLE SWITCH FOR REAR SCENE LIGHTS - MULTIPLEX ELECTRICAL	1	BI
30-06-0550		DISABLE SWITCH FOR SIDE SCENE LIGHTS - MULTIPLEX ELECTRICAL	1	BI
30-06-0575		REVERSE (TRANSMISSION) FUNCTIONS - MULTIPLEX ELECTRICAL	1	BI
30-10-0030	>	BACKUP ALARM	1	BI
30-10-0050		BATTERY CONVERTER / CHARGER	1	BI
30-10-0110		ELECTRICAL CIRCUITS	1	BI
30-10-0190		GROUND FAULT CIRCUIT INTERRUPTER (GFCI)	1	BI
30-10-0415	>	LIGHT OSS COMPARTMENT - INCANDESCENT	1	BI
30-10-0527		OUTLETS, 125VAC - THREE (3) INTERIOR DUPLEX	1	BI
30-10-0543		OUTLETS, 12VDC - TWO (2) INTERIOR POWERPOINT	1	BI
30-10-0651	<	RADIO ANTENNA BASE - ONE (1)	1	BI
		SHOP NOTE: One (1) antenna base, with attached coax cable shall be installed on the module roof. The coax cable shall terminate in the PDQ. Access to the antenna base shall be through an adjacent interior module dome light.		
30-10-0721	<	RECEPTACLE SHORELINE INLET-20 AMP, NON-AUTO EJECT	1	BI
		SHOP NOTE: Install 20 amp manual (non-auto eject) shoreline receptacle.		
30-10-0753	<	SIREN, WHELEN 295-HFSA7-REMOTE WITH MICROPHONE	1	BI
		SHOP NOTE: A Whelen 295-HFSA7 remote dual siren amplifier shall be flush-mounted in the master control console located in the cab. The siren shall be capable of hands-free operation and shall be equipped with a noise canceling microphone.		
30-10-0814	<	SIREN SPEAKERS, WHELEN SA315 - IN THE BUMPER OPENING	1	BI
		SHOP NOTE: Whelen dual 100 watt siren speakers shall be installed in the bumper opening.		

PART NO	S	DESCRIPTION	QTY	ID
30-10-0901		SYSTEM ACTIVE AND CHECK OUT LIGHTS - 5 MINUTES	1	BI
30-11-0101	<	LIGHTS, DOME LED (8) Tecniq SHOP NOTE: Eight (8) Tecniq LED (E08-LC10-1) dome lights, shall be installed. Per dwg #9	1	BI
30-11-0151	<	LIGHTS, TECNIQ LED PANEL (2) STREETSIDE - ANGLED SHOP NOTE: Two (2) Tecniq (E30-L010-1) 21 LED lights streetside (Braun #27469). See Dwg #5	1	BI
30-25-0122	<	LIGHTS, ICC / LED CLEARANCE - ON MODULE FRONT - TECNIQ SHOP NOTE: The vehicle shall have five (5) amber Tecniq LED (S33-AA00-1) clearance / ICC lights on the front of the module near the roof line. Per Dwg #1	1	BI
30-25-0123	<	LIGHTS, ICC / LED CLEARANCE - ON MODULE REAR - TECNIQ SHOP NOTE: The vehicle shall have five (5) red Tecniq LED (S33-RR00-1) clearance / ICC lights on the rear of the module near the roof line. Per Dwg #2	1	BI
30-25-3110	<	LIGHTS, FRONT GRILLE - (2) WHELEN 500 SUPER LED - RED W/CLEAR LENS SHOP NOTE: Whelen 500 series red super LED lights w/clear lens IPOS	1	BI
30-25-4123	<	LIGHTS, FRONT MODULE - WHELEN (7)600 - (6)RED, (1)CLEAR LED W/CLEAR LENS SHOP NOTE: Seven (7) Whelen 600 series super LED warning lights with chrome bezels shall be installed on the module front. There shall be six (6) red w/clear lens and one (1) clear lights. R/R/R/W/R/R/R Per dwg #1	1	BI
30-26-3002	< >	LIGHTS, REAR TAIL - WHELEN 600 LED STOP, TURN, HALOGEN BK-UP SHOP NOTE: One (1) pair each of Whelen 600 series led stop/tail lights, turn lights, and halogen back-up lights with chrome bezels shall be installed on the rear of the module. (meets SAE)	1	BI
30-26-6176	<	LIGHTS, REAR MODULE -WHELEN (7)600 -(4)RED, (1)AMB LED, (2)HALO SCN - CLR LENS SHOP NOTE: Four (4) Whelen 600 red super LED lights w/clear lens, two (2) Whelen 600 series halogen scene/load lights, and one (1) Whelen 600 series amber super LED light w/clear lens shall be installed on the rear of the module w/chrome flanges IPOS. See dwg #2	1	BI
30-26-7002		LIGHT, LICENSE PLATE LED	1	BI
30-27-1102	<	LIGHTS, ICC / LED CLEARANCE - ON MODULE SIDE - TECNIQ SHOP NOTE: The vehicle shall have two (2) red Tecniq LED (S33-RR00-1) clearance / ICC lights : one (1) red on each side at the rear of the vehicle which will also function	1	BI

PART NO	S	DESCRIPTION	QTY	ID
		with the turn signals. Per Dwg #3 and #4		
30-27-1121	<	LIGHTS, INTERSECTION FRONT - WHELEN 500 SUPER LED - RED W/CLEAR LENS SHOP NOTE: Two (2) Whelen 500 series red Super LED warning lights, with clear lens, chrome flanges and water-proof connectors, shall be mounted on the front chassis fenders, one (1) on each side.	1	BI
30-27-2007	<	LIGHTS, SIDE MODULE SCENE - WHELEN 900 HALOGEN - CLEAR (4) SHOP NOTE: Four (4) Whelen 900 series (gradient optics) halogen scene lights with chrome flanges shall be installed, two (2) each module side, inboard of the warning lights.	1	BI
30-27-3009	<	LIGHTS, SIDE MODULE WARNING - WHELEN 900 SUPER LED - RED W/CLR LENS SHOP NOTE: Four (4) Whelen 900 series red super LED warning lights with clear lenses and chrome flanges shall be installed, two (2) each module side, outboard of the side module scene lights. Per dwg #3 & #4	1	BI
30-27-4115	<	LIGHTS, INTERSECTION REAR - WHELEN 700 SUPER LED - RED W/CLR LENS SHOP NOTE: Two (2) Whelen 700 series red super LED warning lights with clear lenses, chrome flanges and water-proof connectors, shall be installed above the rear wheel wells, one (1) on each side Per Dwg #3 & #4	1	BI
39-00-0001		MODULE BODY CONSTRUCTION - SEAMLESS	1	BI
39-00-0005		AWS ALUMINUM CERTIFIED WELDERS	1	BI
39-10-0003		CONNECTIONS, MODULE	1	BI
40-00-0009		ALUMINUM PARTS - MODULE EXTERIOR	1	BI
40-00-0010		CORROSION MINIMIZATION - MODULE	1	BI
40-00-0019	<	DOOR SKINS, OUTSIDE STORAGE COMPARTMENTS - DIAMOND PLATE INTERIOR SKINS SHOP NOTE: The interior door skins for all outside storage compartments shall be constructed of .063" thick aluminum diamond plate.	1	BI
40-00-0020		DOOR CONSTRUCTION - GASKET PLACEMENT	1	BI
40-00-0030		EXTERIOR COMPARTMENTS DESIGN	1	BI
40-00-0051		EXTERIOR COMPARTMENTS, VENTING	1	BI
40-00-0055		EXTERIOR COMPARTMENTS, VENTING - OXYGEN STORAGE	1	BI
40-00-0061		EXTERIOR COMPARTMENTS - SWEEP-OUT	1	BI
40-00-0070		HANDLES, EBERHARD - CHROME FREE FLOATING TYPE	1	BI
40-00-0080		INSULATION - POLYURETHANE SPRAY FOAM	1	BI
40-00-0091		THRESHOLD, STAINLESS STEEL - EXTERIOR STORAGE COMPARTMENT	1	BI
40-10-0066		DOOR SLIDING - MODULE CURBSIDE PASSAGE	1	BI

PART NO	S	DESCRIPTION	QTY	ID
40-10-0072		LOWERED MODULE SIDES	1	BI
40-10-0083		DOORS - REAR PASSAGE	1	BI
40-10-0103		FENDERETTES - POLISHED ALUMINUM	1	BI
40-10-0120	<	HOLD-OPEN - REAR DOORS - GRABBERS	1	BI
		SHOP NOTE: Door grabbers (1 pair) with hard rubber inserts shall be installed on the rear doors. Reference dwg #2 for location.		
40-10-0190		LOCKS, MANUAL (NO POWER DOOR LOCKS)	1	BI
40-10-0204		MUD FLAPS, REAR - BLACK RUBBER FIBERGLASS REINFORCED - THREE COLOR BRAUN LOGO	1	BI
40-10-0266		REAR STEP/BUMPER -FLIP-UP CENTER SECTION - STAR PUNCHED AND ANODIZED	1	BI
40-10-0280	<	RUB RAILS, ANODIZED ALUMINUM	1	BI
		SHOP NOTE: Bright dip anodized polished aluminum rub rails shall be installed on the lower sides of the body below the outside compartment sill areas. The rub rails shall be offset 3/16" from the body to facilitate wash down of road debris.		
40-10-0322	<	STEPWELL, CURBSIDE DOORWAY	1	BI
		SHOP NOTE: The curbside doorway step area shall be covered with a washable sprayed-on multi-use polychromatic coating.		
40-10-0340		STONE GUARDS, MODULE FRONT - ANODIZED DIAMOND PLATE (24" H)	1	BI
40-10-0360	<	KICKPLATE/THRESHOLD, REAR DOORWAY - ANODIZED DIAMOND PLATE	1	BI
		SHOP NOTE: A bright dip anodized aluminum diamond plate kick plate shall be installed at the rear exterior doorway, providing a kick / scuff plate at the rear of the vehicle above the rear step, per dwg. # 2.		
40-10-0505		WINDOWS, PASSAGE DOOR - (CURB SLIDING, REAR FIXED)	1	BI
41-01-0303		OUTSIDE STORAGE #1 - STREETSIDE FORWARD - BACKBOARD STORAGE	1	BI
42-01-0304		OUTSIDE STORAGE #2 - STREETSIDE REAR	1	BI
43-01-0302		OUTSIDE STORAGE #3 - CURBSIDE REAR - OXYGEN CYLINDER STORAGE	1	BI
50-00-0201		ROUNDED INTERIOR CORNERS	1	BI
50-01-0405	<	LATCHES CABINET - CHROME	1	BI
		SHOP NOTE: Install chrome locking lever latch on ACP and PDQ doors		
50-10-0126		CABINET - LEFT WALL, UPPER REAR #1 - FIXED FRAME	1	BI
50-10-0226	<	LEFT WALL - ATTENDANT CONTROL PANEL - HINGED PANEL	1	BI
		SHOP NOTE: The color micro processor screen shall be installed on a hinged access panel and secured with two (2) locking lever latches. The panel will be located to the immediate right of the attendant's seat.		

PART NO	S	DESCRIPTION	QTY	ID
50-10-0324		CABINET - LEFT WALL, UPPER OVER PANEL #2 - FIXED FRAME	1	BI
50-10-0517		CABINET - LEFT WALL, LOWER FORWARD #3	1	BI
50-20-0305		CABINETS - FRONT WALL, UPPER #1 & #2	1	BI
50-20-0310		CABINET - FRONT WALL, LOWER #3	1	BI
50-20-0501		CRAWL-THROUGH - CAB TO MODULE	1	BI
50-50-0100	>	ATTN SEAT - DELUXE HIGH BACK, ON SLIDERS, SWIVEL BASE	1	BI
50-50-0301		CPR SEAT - FIXED	1	BI
50-50-0517		SQUAD BENCH BASE STORAGE (COMPARTMENT #1)	1	BI
50-50-0526		SQUAD BENCH LID - WITH SHARPS AND TRASH ACCESS	1	BI
50-50-0542	<	HOLD OPENS - SQUAD BENCH LID - SPRING LOADED TYPE	1	BI
		SHOP NOTE: Two (2) spring loaded type hold -opens shall be installed, one (1) each end of the squad bench lid.		
50-51-1001		CABINET CONSTRUCTION - INTERIOR - ALUMINUM	1	BI
50-51-1011	<	RECESSED ADJUSTABLE SHELF TRACK - CABINETS	1	BI
		SHOP NOTE: Install recessed adjustable shelf track in cabinets.		
50-51-2002	<	CABINET DOORS - CLEAR ACRYLIC	1	BI
		SHOP NOTE: Clear		
50-51-3001	< >	CABINETS/ WALLS - POLYCHROMATIC COATING - MARBLE STONE	1	BI
		SHOP NOTE: Headliner, walls, cabinet faces, and cabinet interiors Zolatone color to be #20-63 Marble Stone		
50-51-4001	<	COUNTER TOP - RECESSED ALUMINUM - POLYCHROMATIC SPRAY COATED	1	BI
		SHOP NOTE: Recessed counter top with Zolatone color to match cabinets		
50-51-5001	<	UPHOLSTERY - SPRADLING "ARCTIC" CHARCOAL #9017	1	BI
		SHOP NOTE: All cushions, head pads and seating surfaces shall be covered with Spradling International "Arctic" Charcoal # 9017 expanded vinyl upholstery material.		
50-51-6001	<	LONPLATE II, NON-SLIP EMBOSSSED SM. GRID - MICA (GRAY) #421	1	BI
		SHOP NOTE: The floor in the patient compartment shall be covered with Lonseal "Lonplate II" non-slip; small grid (embossed) Mica (gray) #421,		
50-60-0015	<	ASPIRATOR / SUCTION - IMPACT# 324 - SELF CONTAINED - COUNTER	1	BI
		SHOP NOTE: An Impact #324 suction system with built-in pump shall be installed on the action wall counter near the attendant's seat.		
50-60-0037		ASSIST HANDLES, (6) BLACK RUBBER	1	BI
50-60-0153	< >	COT FASTENER - STRYKER SINGLE - CENTER POSITION	1	BI
		SHOP NOTE: Install a Stryker single position center mount		

PART NO	S	DESCRIPTION	QTY	ID
50-60-0220		EMBLEMS / SIGNS - REAR PATIENT COMPARTMENT	1	BI
50-60-0254		EXHAUST VENTILATOR, 3-SPEED - MULTIPLEX ELECTRIC SYSTEM	1	BI
50-60-0300		FLOOR CONSTRUCTION- PATIENT COMPARTMENT, NON-WOOD COMPOSITE	1	BI
50-60-0301		FLOORING - COVE	1	BI
50-60-0340		GRAB RAIL, 1-1/4" DIAMETER, (96") OVER COT AREA	1	BI
50-60-0406	>	HEAT/AIR CONDITIONING, MANUAL/AUTO SELECT, 10-SPEED BLOWER	1	BI
50-60-0434	<	I V HANGERS - PERKO TWO (2), WITH VELCRO STRAPS	1	BI
		SHOP NOTE:		
		Two (2) Perko #1309 I.V. hangers shall be provided. One (1) shall be installed near the street side cabinet and one (1) above the squad bench. A Velcro strap shall be provided at each position to stabilize the bag or bottle.		
50-60-0612		OXYGEN OUTLETS (3) WALL - OHIO MEDICAL TYPE	1	BI
50-60-0653	<	OXYGEN SYSTEM, MANUAL SYSTEM	1	BI
		SHOP NOTE:		
		Manual Oxygen System with Regulator.		
50-60-0660		PADDED EDGING PROTECTION	1	BI
50-60-0661		PADS, HEAD AND BACK	1	BI
50-60-0709		SHARPS AND TRASH CONTAINERS - ACCESS THRU SQUAD BENCH LID	1	BI
50-60-0718		SQUAD BENCH FACE - VINYL FLOORING MATERIAL	1	BI
50-60-0730	<	DOOR PANELS - MODULE PASSAGE DOORS - FULL LENGTH - W/ACCESS PANELS	1	BI
		SHOP NOTE:		
		Interior rear and curbside passage door panels to be full length aluminum, Multi-Spec sprayed to match interior color and contain removable latch access panel per dwg. # 6 & # 8. (Total 3).		
50-60-0761		STAINLESS STEEL WALL PROTECTION - INTERIOR STREETSIDE	1	BI
50-60-0820		TURTLE TILE - SKID-RESISTANT MAT, CURBSIDE STEPWELL	1	BI
60-01-0001		PPG PAINT PROCEDURE	1	BI
60-01-0002	<	PAINT MODULE - OEM WHITE	1	BI
		SHOP NOTE:		
		Paint module OEM white to match the chassis		
60-01-0003		CLEAR COATING - MODULE PAINT	1	BI
60-01-0004	>	BUFFING, PAINT - MODULE	1	BI
60-10-0108		CAB - OEM PAINT	1	BI
60-25-0101	<	BLACK REFLECTIVE MATERIAL IN RUB RAILS	1	BI
		SHOP NOTE:		
		Install black reflective material in rub rails.		
60-30-0200		DOOR REFLECTIVITY	1	BI
80-10-0101		KKK-A-1822F COMPLIANCE	1	BI
80-20-0001	<	VEHICLE MANUALS (1) PACKAGE SET	1	BI
		SHOP NOTE:		

[illegible]