

QUOTATION

Penn Care Inc.

Penn Care
1317 North Rd
Niles, OH 44446
330-544-0777
330-544-0022
sales@penncare.net

Sales Rep:

Terms:

Drawing #:

Est. Delivery Date: / /

Customer PO #:

Penalty:

Customer #:

QPF #:

Exp. Date: 03/01/2015

Create Date: 01/30/2015

Rev. Date: / /

Quote No: 10188-0001

01/30/2015

Page 1

PART NO	S	DESCRIPTION	QTY	ID
== Super Chief 2015 Type I / 170" Mod - 15.000 11/06/14 ==			1	BI
00-01-0273	<	TYPE I - AMBULANCE - SUPER CHIEF I - 73" INTERIOR HEADROOM SHOP NOTE: 2015 SUPER CHIEF I - 170" MODULE	1	BI
CHASSIS PACKAGES			1	BI
10-02-0015	<	CHASSIS - INTERNATIONAL 4300 SBA LP 175" WB - 4x2 DRW SHOP NOTE: 2016	1	BI
10-08-0000	<	* * NO CUSTOM CHASSIS REQUIRED * * SHOP NOTE: NO SPECIAL CHASSIS QUOTED	1	BI
20-10-0099		FUEL TANK - FULL UPON FACTORY RELEASE	1	BI
20-10-0101		AIR RIDE SYSTEM, AUTOMATIC LOWERING FEATURE - OEM	1	BI
20-10-0121	>	BUMP STOPS	1	BI
20-10-0211	<	BATTERY - THREE SYSTEM - LP 4300 ON SLIDEOUT TRAY SHOP NOTE: The chassis shall have three (3) OEM batteries installed on a slide out tray enclosed by a diamond plate hinged drop down door in the step cover.	1	BI
20-10-0402	<	CONDENSER AUXILIARY - BOTTOM MOUNT SHOP NOTE: Install a Hoseline bottom mount auxiliary condenser.	1	BI
20-10-0404		SECONDARY COMPRESSOR	1	BI
20-10-0603		ENGINE BLOCK HEATER - OEM PLUG	1	BI
20-20-0122	< >	FLOOR CONSOLE - ANGLED FRONT - REMOVABLE PLATES - ALUMINUM SHOP NOTE: A center floor console manufactured out of aluminum and covered in a black	1	BI

PART NO	S	DESCRIPTION	QTY	ID
		onyx zolatone. The console shall include a raised area for the Weldon Vista display. The lower portion of the console shall contain two (2) drink holders, with the siren installed between them, then to the rear center a recessed storage area for maps and reports.		
20-20-0251		HEAT SHIELDS	1	BI
20-30-0211		MIRRORS, EXTERIOR 7"X15" POWER/HEATED	1	BI
20-30-0810		EXTERIOR CAB STEPS - STAR PUNCHED DIAMOND PLATE	1	BI
20-30-0914	<	STABILIZER BAR REAR - ROADMASTER - INTERNATIONAL CHASSIS	1	BI
		SHOP NOTE: A ROADMASTER anti-sway bar system shall be installed on the rear chassis suspension to provide for improved vehicle stability and cornering control, per dwg. # 1 notation.		
20-40-0206		WHEEL SIMULATORS, STAINLESS STEEL WITH VALVE STEM EXTENSIONS	1	BI
30-06-0002		ELECTRICAL SYSTEM - WELDON V-MUX, MICRO PROCESSOR BASED	1	BI
30-06-0010		VISTA IV MCC - PUSH BUTTON	1	BI
30-06-0015		VISTA IV ACP - PUSH BUTTON	1	BI
30-06-0026		WARNING DISPLAY - MULTIPLEX ELECTRICAL SYSTEM	1	BI
30-06-0050		DAYTIME RUNNING LAMPS - MULTIPLEX ELECTRICAL SYSTEM	1	BI
30-06-0076		MASTER CONTROL CONSOLE (MCC) - MULTIPLEX ELECTRICAL SYSTEM	1	BI
30-06-0101		ATTENDANT CONTROL PANEL (ACP) - MULTIPLEX ELECTRICAL	1	BI
30-06-0126		ELECTRICAL COMPARTMENT (PDQ) - MULTIPLEX ELECTRICAL SYSTEM	1	BI
30-06-0150		SPARE CIRCUIT - MULTIPLEX ELECTRICAL SYSTEM	1	BI
30-06-0175		WIRING HARNESS CONNECTORS - MULTIPLEX ELECTRICAL SYSTEM	1	BI
30-06-0200		RADIO TIE-IN POINTS - MULTIPLEX ELECTRICAL SYSTEM	1	BI
30-06-0225		EMERGENCY MASTER SWITCH - MULTIPLEX ELECTRICAL SYSTEM	1	BI
30-06-0250		CONTROL PANEL SWITCHES - MULTIPLEX ELECTRICAL SYSTEM	1	BI
30-06-0275		MODULE POWER SWITCH - MULTIPLEX ELECTRICAL SYSTEM	1	BI
30-06-0285		MODULE DISCONNECT - MULTIPLEX ELECTRICAL SYSTEM	1	BI
30-06-0300		VOLTMETER - MULTIPLEX ELECTRICAL SYSTEM	1	BI
30-06-0325		FLASHER - MULTIPLEX ELECTRICAL SYSTEM	1	BI
30-06-0350		FLASHING HEADLIGHTS - MULTIPLEX ELECTRICAL SYSTEM	1	BI
30-06-0375		PARK OVERRIDE - MULTIPLEX ELECTRICAL SYSTEM	1	BI
30-06-0400		LOAD MANAGER-SEQUENTIAL SWITCHING SYSTEM - MULTIPLEX ELECTRIC	1	BI
30-06-0425		WARNING LIGHTS SWITCH - MULTIPLEX ELECTRICAL SYSTEM	1	BI
30-06-0450		FRONT CLEAR DISABLE SWITCH - MULTIPLEX ELECTRICAL SYSTEM	1	BI
30-06-0475		CURBSIDE SCENE LIGHTS "ON" WITH CURBSIDE DOOR - MULTIPLEX EL	1	BI
30-06-0500		REAR SCENE LIGHTS "ON" WITH REAR DOORS OPEN - MULTIPLEX ELEC	1	BI
30-06-0525		DISABLE SWITCH FOR REAR SCENE LIGHTS - MULTIPLEX ELECTRICAL	1	BI
30-06-0550		DISABLE SWITCH FOR SIDE SCENE LIGHTS - MULTIPLEX ELECTRICAL	1	BI
30-06-0575		REVERSE (TRANSMISSION) FUNCTIONS - MULTIPLEX ELECTRICAL	1	BI
30-10-0030	>	BACKUP ALARM	1	BI
30-10-0050		BATTERY CONVERTER / CHARGER	1	BI
30-10-0071	< >	CAMERA REAR VIEW - SINGLE SYSTEM - VISTA SCREEN	1	BI
		SHOP NOTE: Install camera system rear view, tied to M-Tech display screen. Per Dwg #2		

PART NO	S	DESCRIPTION	QTY	ID
30-10-0110		ELECTRICAL CIRCUITS	1	BI
30-10-0190		GROUND FAULT CIRCUIT INTERRUPTER (GFCI)	1	BI
30-10-0290	<	LIGHT, ATTENDANT CONTROL PANEL AREA SHOP NOTE: Install light w/integral switch above action area counter. See Dwg #5	1	BI
30-10-0310	<	LIGHT, ELECTRICAL COMPARTMENT (PDQ) SHOP NOTE: A 12 VDC light shall be located in the PDQ. The light shall be wired "battery-hot" to activate when the PDQ door is in the open position. The light shall be off when the door is in the closed position.	1	BI
30-10-0410	>	LIGHT OSS COMPARTMENT - INCANDESCENT	1	BI
30-10-0527		OUTLETS, 125VAC - THREE (3) INTERIOR DUPLEX	1	BI
30-10-0543		OUTLETS, 12VDC - TWO (2) INTERIOR POWERPOINT	1	BI
30-10-0657		RADIO ANTENNA BASES - TWO (2)	1	BI
30-10-0723	< >	RECEPTACLE SHORELINE INLET-SUPER 20 AMP, AUTO EJECT SHOP NOTE: Install a Kusssmaul 20 AMP super auto eject shoreline inlet receptacle with yellow cover on the module exterior (forward street side) near the driver's door.	1	BI
30-10-0753	<	SIREN, WHELEN 295-HFSA7-REMOTE WITH MICROPHONE SHOP NOTE: A Whelen 295-HFSA7 remote dual siren amplifier shall be flush-mounted in the master control console located in the cab. The siren shall be capable of hands-free operation and shall be equipped with a noise canceling microphone.	1	BI
30-10-0800		SIREN SPEAKERS, CAST PRODUCTS - IN FRONT BUMPER	1	BI
30-10-0901		SYSTEM ACTIVE AND CHECK OUT LIGHTS - 5 MINUTES	1	BI
30-11-0101	<	LIGHTS, DOME LED (8) Tecniq SHOP NOTE: Eight (8) Tecniq LED (E08-LC10-1) dome lights, shall be installed. Per dwg #9	1	BI
30-11-0152	<	LIGHTS, TECNIQ LED PANEL (3) STREETSIDE - ANGLED SHOP NOTE: Three (3) Tecniq (E30-L010-1) 21 LED lights streetside (Braun #27469). See Dwg #5	1	BI
30-11-0176	<	LIGHTS, TECNIQ LED PANEL (2) CURBSIDE - ANGLED SHOP NOTE: Two (2) Tecniq (E30-L010-1) 21 LED lights curb side (Braun #27469). See Dwg #5	1	BI
30-25-0122	<	LIGHTS, ICC / LED CLEARANCE - ON MODULE FRONT - TECNIQ SHOP NOTE: The vehicle shall have five (5) amber Tecniq LED (S33-AA00-1) clearance / ICC lights on the front of the module near the roof line. Per Dwg #1	1	BI
30-25-0123	<	LIGHTS, ICC / LED CLEARANCE - ON MODULE REAR - TECNIQ SHOP NOTE: The vehicle shall have five (5) red Tecniq LED (S33-RR00-1) clearance / ICC lights on the rear of the module near the roof line. Per Dwg #2	1	BI

PART NO	S	DESCRIPTION	QTY	ID
30-25-3111	<	LIGHTS, FRONT GRILLE - (2) WHELEN 700 SUPER LED - RED W/CLEAR LENS	1	BI
		SHOP NOTE: Whelen 700 series red super LED lights w/clear lens		
30-25-4201	<	LIGHTS, FRONT MODULE - WHELEN (7)900 - (6)RED, (1)CLEAR LED W/CLEAR LENS	1	BI
		SHOP NOTE: Seven (7) Whelen 900 series super LED lights with chrome flanges shall be installed on the module front. There shall be six (6) red and one (1) center clear light. All lights to have clear lens IPOS		
30-26-3002	< >	LIGHTS, REAR TAIL - WHELEN 600 LED STOP, TURN, HALOGEN BK-UP	1	BI
		SHOP NOTE: One (1) pair each of Whelen 600 series led stop/tail lights, turn lights, and halogen back-up lights with chrome bezels shall be installed on the rear of the module. (meets SAE)		
30-26-5101	<	LIGHTS, REAR WINDOW-LEVEL - WHELEN (2)900 LED - RED W/CLR LENS	1	BI
		SHOP NOTE: Two (2) Whelen 900 series red super LED lights w/clear lenses and chrome flanges shall be installed on the rear of the module at window level, one (1) on each side. Per dwg #2		
30-26-6168	<	LIGHTS, REAR MODULE -WHELEN (5)900, (2)RED, (1)AMB LED, (2)HALO SCN CLR L	1	BI
		SHOP NOTE: Two (2) Whelen 900 series red super LED lights w/clear lens, two (2) Whelen 900 series halogen scene/load lights, and one (1) Whelen 900 series amber super LED light w/clear lens shall be installed on the rear of the module w/chrome flanges IPOS. See dwg #2		
30-26-7002		LIGHT, LICENSE PLATE LED	1	BI
30-27-1102	<	LIGHTS, ICC / LED CLEARANCE - ON MODULE SIDE - TECNIQ	1	BI
		SHOP NOTE: The vehicle shall have two (2) red Tecniq LED (S33-RR00-1)clearance / ICC lights : one (1) red on each side at the rear of the vehicle which will also function with the turn signals. Per Dwg #3 and #4		
30-27-1116	<	LIGHTS, INTERSECTION FRONT - WHELEN 700 SUPER LED - RED W/CLR LENS	1	BI
		SHOP NOTE: Two (2) Whelen 700 series red super LED warning lights, with clear lens, chrome flanges and water-proof connectors, shall be mounted on the front chassis fenders, one (1) on each side. IPOS		
30-27-2007	<	LIGHTS, SIDE MODULE SCENE - WHELEN 900 HALOGEN - CLEAR (4)	1	BI
		SHOP NOTE: Four (4) Whelen 900 series (gradient optics) halogen scene lights with chrome flanges shall be installed, two (2) each module side, inboard of the warning lights.		
30-27-3009	<	LIGHTS, SIDE MODULE WARNING - WHELEN 900 SUPER LED - RED W/CLR LENS	1	BI
		SHOP NOTE: Four (4) Whelen 900 series red super LED warning lights with clear lenses and chrome flanges shall be installed, two (2) each module side, outboard of the side module scene lights. Per dwg #3 & #4		

PART NO	S	DESCRIPTION	QTY	ID
30-27-4115	<	LIGHTS, INTERSECTION REAR - WHELEN 700 SUPER LED - RED W/CLR LENS SHOP NOTE: Two (2) Whelen 700 series red super LED warning lights with clear lenses, chrome flanges and water-proof connectors, shall be installed above the rear wheel wells, one (1) on each side Per Dwg #3 & #4	1	BI
39-00-0001		MODULE BODY CONSTRUCTION - SEAMLESS	1	BI
39-00-0005		AWS ALUMINUM CERTIFIED WELDERS	1	BI
39-10-0003		CONNECTIONS, MODULE	1	BI
40-00-0009		ALUMINUM PARTS - MODULE EXTERIOR	1	BI
40-00-0010		CORROSION MINIMIZATION - MODULE	1	BI
40-00-0019	<	DOOR SKINS, OUTSIDE STORAGE COMPARTMENTS - DIAMOND PLATE INTERIOR SKINS SHOP NOTE: The interior door skins for all outside storage compartments shall be constructed of .063" thick aluminum diamond plate.	1	BI
40-00-0020		DOOR CONSTRUCTION - GASKET PLACEMENT	1	BI
40-00-0030		EXTERIOR COMPARTMENTS DESIGN	1	BI
40-00-0050		EXTERIOR COMPARTMENTS, VENTING	1	BI
40-00-0055		EXTERIOR COMPARTMENTS, VENTING - OXYGEN STORAGE	1	BI
40-00-0060		EXTERIOR COMPARTMENTS - SWEEP-OUT	1	BI
40-00-0070		HANDLES, EBERHARD - CHROME FREE FLOATING TYPE	1	BI
40-00-0080		INSULATION - POLYURETHANE SPRAY FOAM	1	BI
40-00-0091		THRESHOLD, STAINLESS STEEL - EXTERIOR STORAGE COMPARTMENT	1	BI
40-10-0066		DOOR SLIDING - MODULE CURBSIDE PASSAGE	1	BI
40-10-0072		LOWERED MODULE SIDES	1	BI
40-10-0088		DOORS - REAR PASSAGE	1	BI
40-10-0103		FENDERETTES - POLISHED ALUMINUM	1	BI
40-10-0120	<	HOLD-OPEN - REAR DOORS - GRABBERS SHOP NOTE: Door grabbers (1 pair) with hard rubber inserts shall be installed on the rear doors. Reference dwg #2 for location.	1	BI
40-10-0151	<	SWITCH DOOR UNLOCK - HIDDEN IN FRONT GRILLE AREA SHOP NOTE: An exterior hidden door unlock switch shall also be included and located in the front grille area.	1	BI
40-10-0192		LOCKS POWER - PASSAGE, COMPARTMENTS, KEY FOBS	1	BI
40-10-0204		MUD FLAPS, REAR - BLACK RUBBER FIBERGLASS REINFORCED - THREE COLOR BRAUN LOGO	1	BI
40-10-0266		REAR STEP/BUMPER -FLIP-UP CENTER SECTION - STAR PUNCHED AND ANODIZED	1	BI
40-10-0280	<	RUB RAILS, ANODIZED ALUMINUM SHOP NOTE: Bright dip anodized polished aluminum rub rails shall be installed on the lower sides of the body below the outside compartment sill areas. The rub rails shall be offset 3/16" from the body to facilitate wash down of road debris.	1	BI

PART NO	S	DESCRIPTION	QTY	ID
40-10-0321		STEPWELL, CURBSIDE DOORWAY - MID STEP AREA	1	BI
40-10-0340		STONE GUARDS, MODULE FRONT - ANODIZED DIAMOND PLATE (24" H)	1	BI
40-10-0360	<	KICKPLATE/THRESHOLD, REAR DOORWAY - ANODIZED DIAMOND PLATE	1	BI
		SHOP NOTE: A bright dip anodized aluminum diamond plate kick plate shall be installed at the rear exterior doorway, providing a kick / scuff plate at the rear of the vehicle above the rear step, per dwg. # 2.		
40-10-0381		TOW HOOKS, MODULE REAR	1	BI
40-10-0505		WINDOWS, PASSAGE DOOR - (CURB SLIDING, REAR FIXED)	1	BI
41-01-0607		OUTSIDE STORAGE #1 - STREETSIDE FORWARD	1	BI
42-01-0602		OUTSIDE STORAGE #2 - STREETSIDE CENTER	1	BI
42-02-0051	<	SHELF TRACK - EXPOSED - OSS #2	1	BI
		SHOP NOTE: Install exposed shelf track in OSS #2. These exposed tracks shall be welded in place and coated with Gatorhyde for a cleaner look and no exposed fasteners.		
42-02-0107	<	SHELF ONE (1) IN OSS #2	1	BI
		SHOP NOTE: Install one (1) adjustable shelf in OSS #2.		
43-01-0606		OUTSIDE STORAGE #3 - STREETSIDE REAR - TALL DOOR	1	BI
43-02-0051	<	SHELF TRACK - EXPOSED - OSS #3	1	BI
		SHOP NOTE: Install exposed shelf track in OSS #3. These exposed tracks shall be welded in place and coated with Gatorhyde for a cleaner look and no exposed fasteners.		
43-02-0108	< >	SHELF ONE (1) IN OSS #3	1	BI
		SHOP NOTE: Install one (1) adjustable shelf in OSS #3.		
44-01-0607		OUTSIDE STORAGE #4A BOARD/SCOOP, #4B O2 CYLINDER - RT. REAR	1	BI
45-01-0602		OUTSIDE STORAGE #5 - CURBSIDE FORWARD	1	BI
50-00-0202		ROUNDED INTERIOR CORNERS	1	BI
50-01-0407	<	LATCHES CABINET - CHROME / STAINLESS STEEL	1	BI
		SHOP NOTE: Install chrome locking lever latch on ACP, PDQ, and radio cabinet doors. Install Southco stainless steel locking flush pull latches on all other interior drawers and doors.		
50-10-0114	<	CABINET - LEFT WALL, UPPER REAR #1 - FIXED FRAME	1	BI
		SHOP NOTE: The cabinet shall contain a center fixed divider with one (1) adjustable shelf on each side.		
50-10-0221	<	CABINET - LEFT WALL, UPPER OVER PANEL #2 - FIXED FRAME	1	BI
		SHOP NOTE: The cabinet shall contain a center fixed divider with one (1) adjustable shelf on each side.		

PART NO	S	DESCRIPTION	QTY	ID
50-10-0229	<	LEFT WALL - ATTENDANT CONTROL PANEL - HINGED PANEL SHOP NOTE: The color micro processor screen shall be installed on an angled hinged access panel and secured with two (2) latches. The panel will be located to the immediate right of the attendant's seat. The forward portion of the panel will contain a flat area that may be used for future radio mounting etc.	1	BI
50-10-0343		CABINET - LEFT WALL, LOWER REAR #3 - INSIDE/OUTSIDE	1	BI
50-10-0421	<	DRAWERS - LEFT WALL - REAR ACTION AREA (2) DRAWER UNIT #4 SHOP NOTE: A two (2) drawer cabinet unit shall be installed under the second action area on the interior streetside of the module IATS, per dwg. # 5. The drawers shall open towards an expanded width CPR seat and be secured with locking stainless steel flush pull latches.	1	BI
50-10-0603		PRIMARY ACTION AREA	1	BI
50-10-0644		SECONDARY ACTION AREA	1	BI
50-10-0705		DRAWER - SLIDE-OUT / WRITING TABLE STREETSIDE INTERIOR	1	BI
50-20-0143	<	CABINET - FRONT WALL, UPPER #1 SHOP NOTE: This compartment shall be enclosed by one (1) flip-up acrylic door with hold-open. The compartment shall contain one (1) adjustable shelf.	1	BI
50-20-0280	<	CABINET - FRONT WALL, LOWER #2 & #3 - INSIDE/OUTSIDE ACCESS SHOP NOTE: The lower front wall cabinet shall be split into 2 equal sized compartments IPOS. Each compartment shall have one (1) adjustable shelf. Install a third adjustable shelf to be used as a divider between the upper and lower cabinets. Install a removable faceplate between the cabinets to allow for possible future cabinet modifications. See dwg #7	1	BI
50-20-0382	<	CABINET - FRONT WALL, LOWER BELOW PDQ (SINGLE VENTED DOOR) SHOP NOTE: Install one (1) side hinged vented aluminum door on the cabinet below the PDQ. (cabinet door opening towards the rear of the truck). Door to be secured with a chrome locking lever latch.	1	BI
50-20-0504		PARTITION DOORWAY - WITH HINGED DOOR	1	BI
50-30-0111		CABINET - RIGHT WALL, REAR WITH (1) DOOR FACING AISLE #1	1	BI
50-50-0102	<	ATTN SEAT - EVS HiBAC, INTEGRAL CHILD, SWIVEL BASE SHOP NOTE: Seat, Attendant - EVS high back, integral child seat, installed on a swivel base,	1	BI
50-50-0315	<	CPR SEAT - WIDE FIXED SHOP NOTE: CPR seat (30 Inch wide) per dwg #5	1	BI
50-50-0515		SQUAD BENCH BASE STORAGE (COMPARTMENT #2)	1	BI
50-50-0525		SQUAD BENCH LID - WITH SHARPS AND TRASH ACCESS	1	BI
50-50-0541		HOLD OPENS - SQUAD BENCH LID - GAS CYLINDERS	1	BI
50-51-1001		CABINET CONSTRUCTION - INTERIOR - ALUMINUM	1	BI
50-51-1011	<	RECESSED ADJUSTABLE SHELF TRACK - CABINETS SHOP NOTE: Install recessed adjustable shelf track in cabinets.	1	BI
50-51-2001	<	CABINET DOORS - BRONZE ACRYLIC SHOP NOTE: Bronze	1	BI

PART NO	S	DESCRIPTION	QTY	ID
50-51-3001	< >	CABINETS/ WALLS - POLYCHROMATIC COATING - MARBLE STONE SHOP NOTE: Headliner, walls, cabinet faces, and cabinet interiors Zolatone color to be #20-63 Marble Stone	1	BI
50-51-4011	< >	COUNTER TOP - SOLID ACRYLIC - RAVEN BOULDER (BLACK) SHOP NOTE: A Meganite solid acrylic counter top, Raven Boulder (black) #810,	1	BI
50-51-5001	<	UPHOLSTERY - SPRADLING "ARCTIC" CHARCOAL #9017 SHOP NOTE: All cushions, head pads and seating surfaces shall be covered with Spradling International "Arctic" Charcoal # 9017 expanded vinyl upholstery material.	1	BI
50-51-6003	<	LONPLATE II, NON-SLIP EMBOSSED SM. GRID - GUNMETAL #424 SHOP NOTE: The floor in the patient compartment shall be covered with Lonseal brand "Lonplate II" non-slip; small grid (embossed) Gunmetal #424,	1	BI
50-60-0014	< >	ASPIRATOR / SUCTION - IMPACT #324 SELF-CONTAINED - RECESSED SHOP NOTE: An Impact #324 suction system with built-in pump shall be recessed into the street side lower interior wall near the attendant seat. The recessed area to be large enough for the dealer to change out the suction unit to a SSCOR VX-2.	1	BI
50-60-0037		ASSIST HANDLES, (6) BLACK RUBBER	1	BI
50-60-0153	< >	COT FASTENER - STRYKER SINGLE - CENTER POSITION SHOP NOTE: Install a Stryker single position center mount	1	BI
50-60-0220		EMBLEMS / SIGNS - REAR PATIENT COMPARTMENT	1	BI
50-60-0256		EXHAUST VENTILATOR, 3-SPEED - MULTIPLEX ELECTRIC SYSTEM	1	BI
50-60-0300		FLOOR CONSTRUCTION- PATIENT COMPARTMENT, NON-WOOD COMPOSITE	1	BI
50-60-0301		FLOORING - COVE	1	BI
50-60-0322		GLOVE DISPENSER - (3) BOX - ABOVE ENTRY DOOR - CURBSIDE	1	BI
50-60-0340		GRAB RAIL, 1-1/4" DIAMETER, (96") OVER COT AREA	1	BI
50-60-0391		HEADLINER - REAR PATIENT COMPARTMENT	1	BI
50-60-0424	<	HEAT/AIR CONDITIONING, HOSELINE FT-454 4X4 AC/HEAT CORE SHOP NOTE: Install Hoseline FT-454 with 4x4 AC/Heat Core. (std)	1	BI
50-60-0431	<	I V HANGERS - CEILING RECESSED - CAST PRODUCTS #IV2008-1 (2) SHOP NOTE: Two (2) Cast Products #IV2008-1 recessed, dual ceiling I.V. hangers shall be provided per Dwg #9 locations.	1	BI
50-60-0613	<	OXYGEN OUTLETS (2) WALL/(1)CEILING - OHIO MEDICAL TYPE SHOP NOTE: Three (3) Ohio Medical flush mounted, quick release outlets shall be installed. One (1) in the forward street side cabinet action area, one (1) shall be installed in the wall above the squad bench and one (1) shall be installed in the ceiling above the head end of the cot.	1	BI
50-60-0629	<	FLOW METER, OXYGEN - THORPE STYLE SHOP NOTE: One (1) Thorpe style oxygen flow meter shall be shipped loose with the completed vehicle. (Braun #15920)	1	BI

PDF created with pdfFactory trial version www.pdffactory.com