

DEALER: XYZ Dealer
 CUSTOMER: XYZ Customer
 Street or P.O. Box _____
 City, State, Zip _____
 Customer Contact: _____
 Sales Associate: _____
 Sales Engineer: _____
 VIN#: To be assigned by MEDIX

Chassis Model Yr		2021
MEDIX Model		Metro Express 153 Type I
CHASSIS		Chevy/GMC C-3500, 6.6L Duramax Diesel, 171" WB 84.5"CA 14,000 GVWR 4x2
BODY		153"L x 94" W x 72" Interior Headroom
QTY	STD/OPT	Description
1	15-1000-CD	Chassis & Conversion
	01-	Flooring & Interior Colors
1	STD	Cabinets: Laminated Wood- (Specify Color) Color: _____
1	STD	Upholstery: (Specify Color) Color: _____ Brand: EVS
1	STD	Flooring: Lonseal - Lonfloor Moonstone #507
	02-	Body & Chassis
1	STD	This chassis is equipped with a Diesel Exhaust Fluid (DEF) System to meet the EPA standards for diesel exhaust emissions
1	STD	Anti-Theft Device: IdleLock Ignition Security System, PN: A-IDLE655-A for C/K 3500 Series Chassis Only. Locate activation button to the right side of the steering wheel.
1	STD	All Exterior compartments coated with light gray colored rubberized urethane material.
1	STD	Pass-Thru Window
1	STD	Fender Flares: Black Rubber
1	99-2688	Electric Step: Lippert 24" Single Tread Lite Power Step #353542 mounted below the curbside entry door. There will be a step override switch PN: MX09182 mounted in a single position Positron panel PN: MX01511 installed on the curbside wall above the squad bench just aft of the side entry door. The electric step will automatically extend and retract with side entry door opening/closing.
1	STD	Compartment Lights: Optronics ILL36CB LED Compartment lights-ALL Models
		Locate: (1) Ceiling of Compt #1; (2) in Compt #2- (1) URH, (1) LLH; (1) in ceiling of Compartment #3; (2) in Compt #4/5; (1) in Compt #6.
1	STD	Compartment #1 SS Forward: <u>Smooth Aluminum</u> body, <u>ADP interior door panel</u> , O2 "M" cylinder storage for STEEL tank, Door w/rubber socket/nylon ball hold-open.

1	STD	Compartment #2 SS Center: <u>Smooth Aluminum</u> body, <u>ADP interior door panel</u> , Open Storage, Door w/gas strut hold-open and Seat Belt Strap.
1	STD	Compartment #3 SS Rear: <u>Smooth Aluminum</u> body, <u>ADP interior door panel</u> , Mid-height open storage. Door w/gas strut hold-open.
2	STD	Rear Entry Doors: Single piece laminated smooth aluminum door liner w/stainless steel center panel for black paddle handles; ADP kick panels.
1	STD	Compartment #4/5 CS Forward: NO body <u>above floor</u> , <u>ADP interior door panel</u> , ALS Cabinet w/ Inside/Outside access, Full-height, single Door w/gas strut hold-open. Bottom section smooth aluminum body, Open storage.
1	STD	Curbside Entry Door: Single piece, laminated smooth aluminum door liner w/stainless steel center panel for black paddle handles; ADP kick panels. Gas strut door hold-open. Smooth aluminum stepwell w/Dri-Dek insert.
1	STD	Compartment #6 CS Rear: <u>Smooth Aluminum</u> , Vertical backboard storage w/2 belts. Door w/ rubber socket/nylon ball hold-open. NOTE: NEW STANDARD 77.75" DOOR HEIGHT. Tub PN 71-115267. Door PN 41-115268
1	STD	All Entry Door paddle handle and rotary latching components will include emergency door releases located top and bottom of each door and shall meet the FMVSS 206 30G Test Requirement
1	STD	Rear Bumper: ADP corner pods w/ rubber Dock bumper pads, Center grip-strut flip-up step, powder coated steel frame
2	STD	IV Hangers: Cast black rubber fold-down of knee area of Cot and Squad Bench
3	STD	Mirrors, OEM: (1) each cab door, (1) on interior windshield
1	STD	OEM Chrome wheel covers
4	STD	Stone Guards, lower body corners, ADP
1	STD	Rub Rails: C-Channel, tapered ends, Lower Body off-set mount with neoprene spacers.
2	STD	Aluminum Running Boards: "Starburst" Grip Punched, Diamond Plate, Type 1
1	STD	Cast aluminum fuel fill bezel; DEF fill is under the hood
1	STD	Insulation: Pink, double sided radiant barrier/acoustic material, installed on curbside and streetside rear wheel wells.
1	STD	Insulation: Spray in place foam, FR 2-Part Spray Foam, CP-1000 Kit 200, applied to curbside entry step well and both rear wheel wells
1	STD	Undercoating: Per OEM Guidelines
	03-	Brake, Turn & Back-Up Lights
1	STD	Lights: DOT, Brake/Tail, Turn, Back Up: Whelen 600 Series LED.
1	STD	DOT Marker Lights: TecNiq LED, rubber grommet bezels; (7) S34-AC09-1 Amber- (5) on front of body as Marker lights, (2) side facing on rear extrusions as Turn Signals; (7) S34-RC90-1 Red- (5) on rear of Body as Marker lights, (2) side facing as Turn Signals.
	04-	Electrical, Power Distribution, Control Center & Interior Lighting
1	STD	Battery Switch, Automatic: TST CDR-400. NOTE: Locate in Electrical Cabinet.

2	STD	Antenna, Radio Coax Cable terminated behind driver's seat w/Power & Ground for each
1	STD	(1) Camera System: RVS Systems RVS-MV3-IR Surface Mount Backup Camera with Infra-Red Illuminators, RVS-OA04 OEM harness adapter and connector for GM C/K 3500.
8	STD	Lights: Dome, Whelen LED, 18-diodes w/chrome flange MX80EHZA , switched separately with Hi/Lo functions.
1	STD	Action Area Light: Whelen PSC0ADCR, 12 VDC LED Strip light, 6 diodes and On/Off switch on rear control panel
1	STD	USB Port: Vanner VSS-USB dual port 2Amp mounted on A/A wall
1	STD	Shoreline: 125 VAC, 20-Amp, 60 Hz straight-blade inlet w/hinged, weatherproof cover, located to rear of Compartment #1
1	STD	Inverter: Pre-Wire w/switch on rear panel. Pre-wire located in lower pass-thru cabinet
1	STD	Battery Conditioner, Power Source, 45-Amp- In Lower WT cabinet
1	STD	Timer: 5-minute check-out, wired to CS Hight mode dome lights
1	STD	Breaker Box: 125 VAC w/20-Amp Breaker located on the rear wall of interior cabinet E. GFI receptacle located on the Action Area wall.
2	STD	12 VDC Outlets: (1) in Action Area, (1) in ALS Cabinet
2	STD	125 VAC Outlets, Duplex: (1) in Action Area, (1) in ALS Cabinet
1	STD	Rear Switch Panel: Engraved black plastic panel with (10) LED lighted switch positions for Dome Lights (2), Vacuum (1), Vent (1), A.A. Light (1), Inverter (1), <u>Spare switches and digital clock w/Mode Buttons. MX01517.</u>
1	STD	Front Console: Formed Aluminum, black powder coated, attached to floor. Switch panel with siren panel to rear
1	STD	Electrical Cabinet: Located over pass-thru w/latching, recessed, vented door
	05-	Warning Lights & Siren
1	STD	Lights: Warning, Whelen LED EMERGENCY Lighting Package- Ford, Chevy <u>Type I and Type III</u>- Models ONLY. NOTE: Does not include LED Scene Lights.
		All LED lights shall have CLEAR Lenses. All emergency and scene lighting shall have chrome flanges in standard locations.
		<u>Front of Body:</u> Add (7) Whelen 900 Series Suprer-LEDs- Specify pattern by LED Color (Red or White: _____ Outer (2) lights and (1) Center light flash on K-Spec flasher. Inner (4) flash independently on Light Bar switch on front console.
		<u>Sides of Body:</u> (4) Whelen 900 Series Red Super-LEDs: (2) each side in upper corners
		<u>Rear of Body:</u> (4) Whelen 900 Series Red Super-LEDs: (2) in upper outboard corners, (2) Mid-Body wired as Warning/Brake at the window level; (1) Whelen 900 Series Amber Super-LED in the center position over the rear doors.
		<u>Brake, Turn & Back-Up Lights:</u> Whelen 600 Series LEDs
		<u>Lights, Warning, Intersection Lights:</u> (2) Whelen LINZ6R Series Red Super-LEDs on front fenders
2	STD	Lights, Warning, Grille: WIONSMCR Red LED w/clear lenses & chrome flanges on center grille bar.

4	STD	Lights: Scene, Whelen 900 Series Halogen with flange included - (2) Each Side of Module
2	STD	Lights: Scene/Load, Whelen 900 Series Halogen with chrome flange.
1	STD	Flasher- For Warning Light System, Vanner 9860GCPE
2	STD	Siren Speakers: Dual 100-watt drivers mounted through front bumper
1	STD	Siren- Whelen 295 SLA1, 200 Watt
	06-	Oxygen, Vacuum & Miscellaneous Items
3	STD	Oxygen Outlets: Quick-connect style, (2) in Action Area, (1) over Squad Bench
1	STD	Suction Aspirator System: Rico disposable container, mounted in Action Area w/gauge and quick-connect; SSCOR vacuum pump mounted in lower pass-thru cabinet
1	STD	Oxygen Cylinder Retention: For "M" cylinder, black steel w/3-spring buckle straps and top collar, located in Compartment #1
1	STD	O2 Regulator, Amvex, 50psi, pre-set
	07-	AC/Heat
1	STD	HVAC System: High capacity ProAir, brushless free blow combination Heat-AC system with digital thermostat control on the action area wall. HVAC unit is mounted in bulkhead at the top of the ALS.
	08-	Cabinets, Hardware & Miscellaneous Items
1	STD	Main Streetside Wall Cabinets: Specify desired configuration-
0	STD	Full Wall of Cabinets
0	OPT	Cabinet Configuration- CPR Seat w/EVS V-4 seat belt system and 2nd Action Area; includes (1) 125VAC and (1) 12VDC outlet in 2nd Action Area
		Main Wall Cabinets will have (1) adjustable shelf in each and sliding polycarbonate doors with full height extruded handles. See Prints for Configuration.
1	STD	Cabinet, Rear Overhead: Cabinet over rear door opening w/polycarbonate sliding doors w/full height extruded handles.
1	STD	Action Area Overhead Cabinet: Single cabinet full-height/full-depth of Action Area with sliding polycarbonate doors and full height extruded handles.
1	STD	Action Area and Switch Panel: Laminated, sealed countertop and vertical panel with Suction system collection canister, Vacuum gauge, (2) Oxygen outlets, (1) USB, (1) 12VDC Outlet, (1) 125VAC Outlet and digital Thermostat. Switch panel MX01517 includes (10) switch positions and digital clock w/Mode Buttons.
2	STD	Bulkhead Wall Cabinets: Electrical Cabinet above walk-thru w/hinged, latching, vented door.
2	STD	Pass-Thru Cabinets: Upper cabinet- general storage w/hinged, latching door; Lower cabinet- general storage w/hinged, latching, vented door and location for inverter and vacuum pump on floor.
1	STD	ALS Cabinet: Lower section- Locking storage for 747 box; Middle Section- General storage hinged, non-locking doors and 1-adjustable shelf
1	STD	Squad Bench:

	1	Full length hinged lid w/TriMark latch for access to interior storage.
	2	Full length upholstered seat cushion except over Sharps/Waste Area; formed upholstered back rest cushions and head pad for each seated position.
	3	(2) EVS V-4 Belted seating positions w/progressive foam back and head pads and (3) short bottom straps for 2nd Patient restraint.
	4	Stainless steel kick plate on lower, aisle side face.
1	STD	Sharps/Waste: Drop-in style with aluminum, powder coated red, hinged lid and standard containers, located at head of squad bench.
1	STD	Technician's Seat: EVS Rear facing automotive style chair with V-4 belt system mounted on steel base w/side access to storage.
1	STD	Assist Rail, overhead off-center toward Streetside of unit.
3	STD	Grab handle- stainless steel, mounted on each rear entry and curbside entry door
8	STD	Reflective Striping, Door Open Protection: .50" Red reflective striping around interior door pan of all body doors.
	09-	Cots & Miscellaneous Items
0	STD	Cot Mount: NOTE - Must supply cot mount requirements with order.
	10-	Paint & lettering
1	STD	Paint: Body all OEM White
0	1000100	Roof Star ONLY, INSTALLED
		SHIP LOOSE
2	STD	5 lb. Fire Extinguisher- Ship Loose

TOTAL ORDER

I have reviewed this Order and find it to be acceptable and ready to build.

 Dealer Signature **Date:** _____

I have reviewed this Order and find it to be acceptable and ready to build with the addition of the attached, approved changes.

 Dealer Signature **Date:** _____

Due to on-going product improvements and the changing requirements of the ambulance industry, MEDIX Specialty Vehicles, Inc. reserves the right to change product specifications and related products without prior notice and without any obligation to change prior products or parts. ALL PATENTS RIGHTS RESERVED.