



MSVI Unit #:  
XX-XXXX

DEALER: XYZ Dealer  
 CUSTOMER: XYZ Customer  
 Street or P.O. Box \_\_\_\_\_  
 City, State, Zip \_\_\_\_\_  
 Customer Contact: \_\_\_\_\_  
 Sales Associate: \_\_\_\_\_  
 Sales Engineer: \_\_\_\_\_  
 VIN#: To be assigned by MEDIX

Chassis Model Yr		<b>2021</b>
MEDIX Model		Metro Express RP-90 ES, Type III
CHASSIS		Chevy/GMC 3500 Cutaway, 6.6L DI Gasoline, 139" WB 12,300 GVWR
BODY		146"L x 90"W x 68" Interior Headroom
QTY	STD/OPT	Description
1	15-90ES-CD	Chassis & Conversion
<b>01-</b>		<b>Flooring &amp; Interior Colors</b>
1	STD	Cabinets: Laminated Wood- (Specify Color) Color: _____
1	STD	Upholstery: (Specify Color) Color: _____ Brand: <b>EVS</b>
1	STD	Flooring: Lonseal - Lonfloor Moonstone #507
<b>02-</b>		<b>Body &amp; Chassis</b>
1	STD	This chassis is equipped with a Gasoline Exhaust System to meet the EPA standards for Gasoline exhaust emissions
1	STD	Anti-Theft Device: IdleLock Ignition Security System, PN: A-IDLE611 for G-3500/4500 Series Chassis Only. Locate activation button to the right side of the steering wheel.
1	STD	All Exterior compartments coated with light gray colored rubberized urethane material.
1	STD	Walk-Thru w/Sliding Door. Slides behind driver's seat
1	STD	Fender Flares: Black rubber
1	STD	Compartment Lights: Optronics ILL36CB LED Compartment lights- ALL Models
		Locate: (1) Ceiling of Compt #1; (2) in Compt #2- (1) URH, (1) LLH; (1) in ceiling of Compartment #3; (2) in Compt #4/5; (1) in Compt #6 (if ordered).
1	STD	Compartment #1 SS Forward: <u>Smooth Aluminum</u> body, <u>ADP interior door panel</u> , O2 "M" cylinder storage for STEEL tank, Door w/rubber socket/nylon ball hold-open.
1	STD	Compartment #2 SS Center: <u>Smooth Aluminum</u> body, <u>ADP interior door panel</u> , Open Storage, Door w/gas strut hold-open and Seat Belt Strap. Order Gas chassis tub #41-101223

1	STD	Compartment #3 SS Rear: <u>Smooth Aluminum</u> body, <u>ADP interior door panel</u> , Vertical backboard storage w/2- belts. Door w/2" nylon strap hold-open.
2	STD	Rear Entry Doors: Single piece laminated smooth aluminum door liner w/stainless steel center panel for black paddle handles; ADP kick panels.
1	STD	Compartment #4/5 CS Forward: NO body <u>above floor</u> , <u>ADP interior door panel</u> , ALS Cabinet w/ Inside/Outside access, Full-height, single Door w/gas strut hold-open, Bottom section aluminum body w/roll-out battery tray w/removable, latching door.
1	STD	Curbside Entry Door: Single piece, laminated smooth aluminum door liner w/stainless steel center panel for black and chrome paddle handles; ADP kick panels. Gas strut door hold-open. Smooth aluminum stepwell w/Dri-Dek insert.
1	STD	All Entry Door paddle handle and rotary latching components will include emergency door releases located top and bottom of each door and shall meet the FMVSS 206 30G Test Requirement
1	STD	Rear Bumper: ADP corner pods w/Dock bumper pads, Center grip-strut flip-up step, powder coated steel frame
2	STD	IV Hangers: (2) Cast black rubber fold-down of knee area of Cot and Squad Bench
2	STD	<b>Mirrors, Velvac, 2020XG for G-series cutaway with 8D8 option, Heated/Remote Deluxe head w/bottom convex, no turns, Black, Kit# 718416</b>
1	STD	<b>OEM Chrome wheel covers</b>
4	STD	Stone Guards, lower body corners, ADP
2	STD	Running Boards, formed ADP with front splash guards
1	STD	Rub Rails, C-Channel, tapered ends, Lower Body off-set mount with neoprene spacers.
2	STD	Cast aluminum fuel fill bezels
1	STD	<b>Insulation: Pink, double sided radiant barrier/acoustic material, installed on curbside and streetside rear wheel wells.</b>
1	STD	<b>Insulation: Spray in place foam, FR 2-Part Spray Foam, CP-1000 Kit 200, applied to curbside entry step well and both rear wheel wells</b>
1	STD	Undercoating: Per OEM Guidelines
	<b>03-</b>	<b>Brake, Turn &amp; Back-Up Lights</b>
1	STD	<b>Lights: DOT, Brake/Tail, Turn, Back Up: Whelen 600 Series LED.</b>
1	STD	DOT Marker Lights: TecNiq LED, rubber grommet bezels; (7) S34-AC09-1 Amber- (5) on front of body as Marker lights, (2) side facing on rear extrusions as Turn Signals; (7) S34-RC90-1 Red- (5) on rear of Body as Marker lights, (2) side facing as Turn Signals.
	<b>04-</b>	<b>Electrical, Power Distribution, Control Center &amp; Interior Lighting</b>
1	STD	Battery Switch, Automatic: TST CDR-400. Located in Electrical Cabinet.
2	STD	Antenna, Radio Coax Cable terminated behind driver's seat w/Power & Ground for each

1	STD	<b>1 Camera System:</b> RVS RVS-770-09 130 degree backup camera with infra-red illuminators and GM adapter harness. <b>NOTE:</b> For GM3500/4500 with OEM back up prewire and monitor system. <b>Locate:</b> Camera mounted off lower RH corner of center rear Amber light.
8	STD	<b>Lights: Dome, Whelen LED, 18-diodes w/chrome flange MX80EHZA , switched separately with Hi/Lo functions.</b>
1	STD	Action Area Light: Whelen PSC0ADCR, 12 VDC LED Strip light, 6 diodes and On/Off switch on rear control panel
1	STD	USB Port: Vanner VSS-USB dual port 2Amp mounted on A/A wall
1	STD	Shoreline: 125 VAC, 20-Amp, 60 Hz, straight blade inlet w/hinged, weatherproof cover, located above Compartment #2 SS
1	STD	Timer: 5-minute check-out, wired to CS High mode dome lights
1	STD	Inverter: Pre-Wire w/switch on rear panel. Pre-wire located in lower pass-through cabinet
1	STD	Battery Conditioner, Power Source, 45-Amp- Lower pass-through cabinet
1	STD	Breaker Box: 125 VAC w/20-Amp Breaker located behind the driver's seat base. GFI receptacle located on the Action Area wall.
2	STD	12 VDC Outlets: (1) in Action Area, (1) in ALS Cabinet
2	STD	125 VAC Outlets: Duplex, located 1-in Action Area, 1- in ALS
1	STD	Rear Switch Panel: Engraved black plastic panel with (10) LED lighted switch positions for Dome Lights (2), Vacuum (1), Vent (1), A.A. Light (1), Inverter (1), <u>Spare switches and digital clock w/Mode Buttons. MX01517.</u>
1	STD	Front Console: CNC cut, formed and powder coated aluminum secured to floor; revmovable switch and siren panels for maintenance.
1	STD	Electrical Cabinet: Located over pass-through w/latching, recessed, vented door
	<b>05-</b>	<b>Warning Lights &amp; Sirens</b>
1	STD	<b>Lights: Warning, Whelen LED EMERGENCY Lighting Package-Ford, Chevy <u>Type I and Type III</u>- Models ONLY.</b> <b>NOTE: Does not include LED Scene Lights.</b>
		<b>All LED lights shall have CLEAR Lenses. All emergency and scene lighting shall have chrome flanges in standard locations.</b>
		<b><u>Front of Body:</u></b> Add (7) Whelen 900 Series Suprer-LEDs- Specify pattern by LED Color (Red or White: _____ Outer (2) lights and (1) Center light flash on K-Spec flasher. Inner (4) flash independently on Light Bar switch on front console.
		<b><u>Sides of Body:</u></b> (4) Whelen 900 Series Red Super-LEDs: (2) each side in upper corners
		<b><u>Rear of Body:</u></b> (4) Whelen 900 Series Red Super-LEDs: (2) in upper outboard corners, (2) Mid-Body wired as Warning/Brake at the window level; (1) Whelen 700 Series Amber Super-LED in the center position over the rear doors.
		<b><u>Brake, Turn &amp; Back-Up Lights:</u></b> Whelen 600 Series LEDs
		<b><u>Lights, Warning, Intersection Lights:</u></b> (2) Whelen 700 Series Red Super-LEDs on front fenders.

2	STD	Lights, Warning, Grille: LINZ6R Red LED w/clear lenses & chrome flanges on center grille bar
4	STD	<b>Lights: Scene, Whelen 900 Series Halogen with flange included - (2) Each Side of Module</b>
2	STD	<b>Lights, Load: Whelen 700 Series LED 7SC0ENZR, (2) on rear</b>
1	STD	Flasher- for Warning Light system, Vanner 9860GCPE
2	STD	Siren Speakers: dual 100 Watt drivers mounted through the front bumper
1	STD	Siren- Whelen 295 SLSA1, 200 Watt
	<b>06-</b>	<b>Oxygen, Vacuum &amp; Miscellaneous Items</b>
3	STD	Oxygen Outlets: Quick-connect style, 2-in Action Area, 1-over Squad Bench
1	STD	Suction Aspirator System: Rico disposable container mounted in Action Area w/gauge and quick-connect; SSCOR vacuum pump mounted in lower pass-through cabinet
1	STD	Oxygen Cylinder Retention: For "M" cylinder, black steel w/3-spring buckle straps and top collar, located in Compartment #1
1	STD	O2 Regulator, Amvex, 50psi, pre-set
	<b>07-</b>	<b>AC / Heat</b>
1	STD	<b>HVAC System: High capacity ProAir, brushless free blow combination Heat-AC system with digital thermostat control on the action area wall. HVAC unit is mounted in bulkhead at the top of the ALS.</b>
	<b>08-</b>	<b>Cabinets, Hardware &amp; Miscellaneous Items</b>
1	STD	Main Streetside Wall Cabinets: Specify desired configuration-
0	STD	<b>Full Wall of Cabinets</b>
0	OPT	<b>Cabinet Configuration- CPR Seat w/EVS V-4 seat belt system</b>
		Main Wall Cabinets will have (1) adjustable shelf in each and sliding polycarbonate doors with full height extruded handles. See Prints for Configuration.
1	STD	Action Area Overhead Cabinet: Single cabinet full-height/full-depth of Action Area with sliding polycarbonate doors and full height extruded handles.
1	STD	Action Area and Switch Panel: Laminated, sealed countertop and vertical panel with Suction system collection canister, Vacuum gauge, (2) Oxygen outlets, (1) USB, (1) 12VDC Outlet, (1) 125VAC Outlet and digital Thermostat. Switch panel MX01517 includes (10) switch positions and digital clock w/Mode Buttons.
2	STD	Bulkhead Wall Cabinets: Cabinet above Tech Seat- general storage w/hinged, latching door; Electrical Cabinet located over pass-through w/latching, vented door
1	STD	Bulkhead Cabinets: Upper cabinet- general storage w/hinged, latching door; Lower cabinet general storage w/hinged, latching, vented door and location for inverter and vacuum pump on floor.
1	STD	ALS Cabinet: Lower section- Locking storage for 747 box, Middle Section- General storage with hinged, non-locking doors and 1-adjustable shelf
1	STD	<b>Squad Bench:</b>

	1	Full length hinged lid w/TriMark latch for access to interior storage
	2	Full length upholstered seat cushion except over Sharps/Waste Area; formed upholstered back rest cushions and head pad for each seated position.
	3	(2) EVS V-4 Belted seating positions w/progressive foam back and head pads and (3) short bottom straps for 2nd Patient restraint
1	STD	Sharps/Waste: Drop-in style with aluminum, powder coated red, hinged lid and standard containers, located at head of squad bench.
1	STD	Rear Overhead: Vinyl wrapped foam header over rear doors.
1	STD	Technician's Seat: EVS Rear facing automotive style chair with V-4 belt system mounted on steel base w/side access to storage.
1	STD	Assist Rail, overhead off-center toward Streetside of unit.
3	STD	Grab handle- stainless steel, mounted on each rear entry and curbside entry door
7	STD	Reflective Striping, Door Open Protection: .50" Red reflective striping around interior door pan of all body doors.
	<b>09-</b>	<b>Cots &amp; Miscellaneous Items</b>
<b>0</b>	<b>STD</b>	<b>Cot Mount: NOTE - Must supply cot mount requirements with order.</b>
	<b>10-</b>	<b>Paint &amp; Lettering</b>
1	STD	Paint: Body all OEM White
<b>0</b>	<b>1000100</b>	<b>Roof Star ONLY, INSTALLED</b>
		<b>SHIP LOOSE</b>
2	STD	5 Lb. Fire Extinguisher- Ship Loose is Standard
<b>TOTAL ORDER</b>		

I have reviewed this Order and find it to be acceptable and ready to build.

\_\_\_\_\_  
Dealer Signature

Date: \_\_\_\_\_

I have reviewed this Order and find it to be acceptable and ready to build with the addition of the attached, approved changes.

\_\_\_\_\_  
Dealer Signature

Date: \_\_\_\_\_

Due to on-going product improvements and the changing requirements of the ambulance industry, MEDIX Specialty Vehicles, Inc. reserves the right to change product specifications and related products without prior notice and without any obligation to change prior products or parts. ALL PATENTS RIGHTS RESERVED.