



GEN-T AMBULANCE

Unit #:
20-347-002

DEALER: Penn Care
 CUSTOMER: Demo
 Street or P.O. Box _____
 City, State, Zip _____
 Customer Contact: _____
 Sales Associate: _____
 VIN#: To be assigned by Gen-T

| Chassis Model Yr | | 2021 |
|------------------------------|------------|---|
| Gen-T Model | | Gen-T DB-147 Type III |
| CHASSIS | | Ford E-350 XL Cutaway, 7.3 L V-8 Gas, 138" WB, 11,500 GVWR |
| BODY | | 147"L x 90"W x 70" Interior Headroom |
| QTY | STD/OPT | Description |
| 1 | 16-90ES-FG | Chassis & Conversion |
| | 01- | Flooring & Interior Colors |
| 1 | STD | Cabinets: Laminated Wood- (Specify Color) |
| 1 | 100040 | Laminate: High Gloss Gray |
| 1 | STD | Upholstery: (Specify Color) |
| | | Color: BLACK Brand: EVS |
| 1 | 100020 | Flooring: Lonseal- LonPlate (Diamond Plate) Specify Color: GunPowder 424TX |
| | 02- | Body & Chassis |
| | WELD SHOP | Note: Roof to be .125" thickness. |
| GEN-T Standard Configuration | | |
| 1 | STD | Roof: 2" structural crowned roof, front to rear. |
| 1 | STD | All Exterior compartments coated with a light gray rubberized urethan material. |
| 1 | STD | Anti-Theft Device: IdleLock Ignition Security System, PN: B-IDLE506-A for Ford E Series Chassis Only. Locate activation button to the right side of the steering wheel. |
| 1 | STD | Pass-through w/horizontal sliding window |
| 1 | STD | Fender Flares: Black rubber |
| 1 | STD | Compartment Lights: Optronics ILL36CB LED Compartment lights- ALL Models |
| | | Locate: (1) Ceiling of Compt #1; (2) in Compt #2- (1) URH, (1) LLH; (1) in ceiling of Compartment #3; (1) in Compt #4/5-middle section; (1) in Compt #6 (if ordered). |
| 1 | STD | Compartment #1 SS Forward: Smooth Aluminum body, ADP interior door panel, O2 "M" cylinder storage for STEEL tank, Door w/rubber socket/nylon ball hold-open. |
| 1 | STD | Compartment #2 SS Center: Smooth Aluminum body, ADP interior door panel, Open Storage, Door w/gas strut hold-open and Seat Belt Strap. |

| | | |
|---|---------------|---|
| 1 | NEW DB STD | Compartment #3 SS Rear: <u>Smooth Aluminum</u> body, <u>ADP interior door panel</u> , Includes a seat belt strap across upper/offset section of compartment for backboard storage and a seat belt strap in lower section of compartment centered on back wall for stair chair storage. Nylon strap hold-open. |
| 2 | STD | Rear Entry Doors: Single piece laminated smooth aluminum door liner w/stainless steel center panel for black paddle handles; ADP kick panels. |
| 1 | NEW DB STD | Compartment #4 CS Forward: NO body above floor. ADP Interior door panel, ALS Cabinet w/ Inside/Outside access. Full height Single access door w/gas strut hold-open. Bottom section aluminum body w/roll-out battery tray w/removable, latching door. NOTE: There will be a closeout for the lower portion of the ALS Cabinet so that it is inside access only. Only the upper portion of the ALS cabinet to have inside/outside access. |
| 1 | STD | Curbside Entry Door: Single piece, laminated smooth aluminum door liner w/stainless steel center panel for black and chrome paddle handles; ADP kick panels. Gas strut door hold-open. Smooth aluminum stepwell w/Dri-Dek insert. Single LED Step well light. |
| 1 | 200090 | Compartment #6: CS rear spare tire aft of rear wheel well on RP90ES w/seat belt strap. Smooth Aluminum with rubberized urethane coating, drop floor for tire w/removable cover plate and (1) LED light in ceiling. |
| 1 | STD | All Entry Door paddle handle and rotary latching components will include emergency door releases located top and bottom of each door and shall meet the FMVSS 206 30G Test Requirement |
| 1 | 200200A | Power Door Locks: All Entry and Compartment Doors, wired to OEM door lock system. (Does not include additional lock switches inside module) NOTE: Not for use on MSVII Mods. |
| 1 | 99-0678E | Power Door Locks: Stealth Switch on Ford, Power Door Lock System, Push Button Switch (Grille bracket on E-series: Ford 33-102402) LOCATION: OEM GRILLE |
| 1 | STD | Rear Bumper: ADP corner pods w/Dock bumper pads, Center grip-strut flip-up step, powder coated steel frame |
| 2 | STD | IV Hangers: (2) Cast black rubber fold-down of knee area of Cot and Squad Bench |
| 3 | STD | Mirrors, OEM: (1) each cab door, (1) on interior windshield |
| 1 | STD | Wheel Covers: Stainless steel covers w/Valve Extenders |
| 4 | STD | Stone Guards, lower body corners, ADP |
| 1 | 200277 | Running Boards: "Starburst" Grip Punched, Chevy/GMC, Ford, Sprinter Type III |
| 1 | STD | Rub Rails, C-Channel, tapered ends, Lower Body off-set mount with neoprene spacers. |
| 1 | STD | Cast aluminum fuel fill bezel |

| | | |
|---|----------------|--|
| 1 | STD | Insulation: Pink, double sided radiant barrier/acoustic material, installed on curbside and streetside rear wheel wells. |
| 1 | STD | Insulation: Spray in place foam, FR 2-Part Spray Foam, CP-1000 Kit 200, applied to curbside entry step well and both rear wheel wells |
| 1 | STD | Undercoating: Per QVM Guidelines |
| | | |
| | 03- | Brake, Turn & Back-Up Lights |
| 1 | STD | Lights: DOT, Brake/Tail, Turn, Back Up: Whelen 600 Series LED. |
| 1 | STD | DOT Marker Lights: TecNiq LED, rubber grommet bezels; (7) S34-AC09-1 Amber- (5) on front of body as Marker lights, (2) side facing on rear extrusions as Turn Signals; (7) S34-RC90-1 Red- (5) on rear of Body as Marker lights, (2) side facing as Turn Signals. |
| | | |
| | 04- | Electrical, Power Distribution, Control Center & Interior Lighting |
| | STD | NOTE: Standard M2 Rocker/Relay hardwired electrical system with "L" Series switches, using Gen-T branded Front and Rear electrical panels. All switch panels to have Carbon Fiber Finish. Front Panel MX01611. Rear Panel MX01613. |
| 1 | STD | Battery Switch, Automatic: TST CDR-400. Located in Electrical Cabinet. |
| 2 | STD | Batteries: OEM, 750 C.C.A. |
| | | Locate: (1) Under hood, (1) In roll-out tray in Compartment #4/5 |
| 1 | B.O. #00836 | Front Console/ Switch Panel: Standard Gen-T Type III Console. PN: 44-116473 - Includes Cutout for Digital Thermostat. Locate a ProAir Digital Thermostat (Separate Option) cutout on the top plate of the console. •Includes: -Formed Aluminum body powder coated (black) & fastened to chassis floor. -Gen-T Switch panel: Engraved plastic with LED lighted switches for Emergency Master, Primary/Secondary Modes, Siren/Horn, Left, Rear and Right Floods, Back-Up Alarm, Module Disconnect, PN: 90-114263. -(2) Removable powder coated (black) faceplates: (1) For the standard siren located below switch panel, PN: 44-114892 and (1) Blank removable faceplate located on flat section of console, PN: 44-103421. -(2) Rear cupholders. -Mobile phone/mobile radio cutout between cup holders. -Rear 14" X 3 7/8" x 9 1/2"d storage pocket. NOTE: Front switch panel will have a three way Module Disconnect switch ILOS - see option below. |
| 1 | 99-0988 | USB Port: Kussmaul 091-219-N dual USB port mounted in switch panel. Fits into standard switch slot. IATS LOCATION: Front switch panel |

| | | |
|---|---|--|
| 2 | STD | Antenna, Radio Coax Cable terminated behind driver's seat w/Power & Ground for each |
| 8 | STD | Lights: Dome, Whelen LED, 18-diodes w/chrome flange MX80EHZA , switched separately with Hi/Lo functions. |
| 1 | STD | (1) Camera System: RVS Systems - RVS-MV3-IR - Kit. Includes (1) 7" rear view mirror monitor, (1) flush mount MV1 back-up camera and (1) RVS-826 camera cable. Locate: (1) Camera mounted off lower RH corner of center rear Amber light; Monitor mounted on cab windshield rear view mirror. |
| 1 | STD | Action Area Light: Whelen PSC0ADCR, 12 VDC LED Strip light, 6 diodes and On/Off switch on rear control panel |
| 1 | 99-0617 | Shoreline: 125VAC, Kussmaul 20amp SUPER Auto Eject P/N: 091-55-20-120 side wired w/hinged, yellow, weatherproof cover, Located above Compartment #2 on Streetside. Will have to be mounted on a Kussmaul Stainless Steel E-Z mounting plate P/N: 091-185-009 w/indicator light for ease of access. Mating Connector to be shipped loose. ILOS |
| 1 | 99-0550-A switch panel for Gen-T | Switching: Timer, Momentary 15-Minute timer switch for patient compartment dome lights. Locate switch in Positron switch panel in standard position on curbside wall. (PNs: MX09150 switch, MX09151 Timer, Carbon Fiber single switch panel MX01631) NOTE: A-Line Models Only |
| 1 | STD | Timer: 5-minute check-out, <u>wired to all dome lights</u>, set to high mode. |
| 1 | 400160 | Inverter: Vanner 20-1050CUL- 1000watt w/battery charger and built in GFI. Remote controlled w/switch in rear panel. (This option deletes the GFI in the A/A wall). ILOS Location: Compartment #2 |
| 1 | 400150 | Battery Charger: DELETE STANDARD (when adding Inverter with integral charger) |
| 1 | STD | Breaker Box: 125 VAC w/20-Amp Breaker located in compartment #2. GFI receptacle located on the Action Area wall. |
| 3 | STD | 12 VDC: (1) wall plate with (1) 12VDC outlet and (1) dual 2A USB charging ports, Positron Panel backlit w/Gen-T Logo, PN #MX01626: (1) in Action Area, (1) in ALS Cabinet, (1) Curbside wall above workstation |
| 3 | STD | 125VAC: Duplex Outlet, Grey outlet w/Carbon Fiber finish faceplate: (1) in Action Area, (1) in ALS Cabinet, (1) Curbside wall above workstation |
| 1 | STD | Rear Switch Panel: (1) Rear Carbon Fiber Gen-T Electrical Panel for Dome Lights (2), Vacuum (1), Vent (1), A.A. Light (1), Inverter (1), <u>Spare switches and digital clock w/Mode Buttons.</u> NOTE: Rear switch panel will have a three way Module Disconnect switch - see option below. |

| | | |
|---|------------|--|
| 1 | 99-0898 | Module Disconnect: (3) way module power control with SPDT momentary switch PN: MX09210 (1) in front console and (1) in rear Action Area. Power can be controlled from either location. |
| 1 | STD | Electrical Cabinet: Located over pass-through w/latching, vented door |
| | | |
| | 05- | Warning Lights & Sirens |
| 1 | STD | Lights: Warning, Whelen LED EMERGENCY Lighting Package- Ford, Chevy <u>Type I</u> and <u>Type III</u>- Models ONLY. NOTE: Does not include LED Scene Lights. |
| | | All LED lights shall have CLEAR Lenses. All emergency and scene lighting shall have chrome flanges in standard locations. |
| | | Front of Body: Add (7) Whelen 900 Series Suprer-LEDs- Specify pattern by LED Color (6) Red and (1) White: R-R-R-W-R-R-R. Outer (2) lights and (1) Center light flash on K-Spec flasher. Inner (4) flash independently on Light Bar switch on front console. |
| | | Sides of Body: (4) Whelen 900 Series Red Super-LEDs: (2) each side in upper corners |
| | | Rear of Body: (4) Whelen 900 Series Red Super-LEDs: (2) in upper outboard corners, (2) Mid-Body wired as Warning/Brake at the window level; (1) Whelen 700 Series Amber Super-LED in the center position over the rear doors. |
| | | Brake, Turn & Back-Up Lights: Whelen 600 Series LEDs |
| | | Lights, Warning, Intersection Lights: (2) 700 Series Red LEDs on front fenders |
| 1 | 500210 | Lights: Warning, (2) Whelen 700 Series Super-LED 70R02FCR Red with clear lens and chrome flange 7EFLANGE, IATS above rear wheel wells as rear intersection lights. Wire to Primary circuit only. |
| 2 | STD | Lights, Warning, Grille: LINZ6R Red LED w/clear lenses & chrome flanges on center grille bar |
| 4 | 500127 | Lights: Scene/Load, Whelen 900 Series Super-LED 9SC0ENZR Gradient Opti-Scenelight™ with chrome flange- ILOS Halogen Specify Locations: (2) Streetside (2) Curbside |
| 2 | STD | Lights, Load: Whelen 700 Series LED 7SC0ENZR, (2) on rear |
| 1 | 99-0106 | Lights: Scene/Load, Rear side scene lights on each side to come "ON" in Reverse |
| 1 | STD | Flasher- for Warning Light system, Vanner 9860GCPE |
| 2 | STD | Siren Speakers: dual 100 Watt drivers mounted through the front bumper |
| 1 | STD | Siren- Whelen 295 SLSA1, 200 Watt |
| | | |
| | 06- | Oxygen, Vacuum & Miscellaneous Items |
| 3 | STD | Oxygen Outlets: Quick-connect style, 2-in Action Area, 1-over Squad Bench |

| | | |
|---|---------------------|---|
| 1 | 600100 | Oxygen: OHMEDA Z-QD0101M0 outlet, IATS Specify Location(s): In recessed ceiling, standard position |
| 1 | NEW DB STD | Suction Aspirator System: SSCOR disposable container w/SSCOR gauge and quick-connect mounted in Action Area w/gauge and quick-connect; SSCOR vacuum pump mounted in compartment #2. |
| 1 | STD | Oxygen Cylinder Retention: For "M" cylinder, black steel w/3-spring buckle straps and top collar, located in Compartment #1 |
| 1 | STD | O2 Regulator, Amvex, 50psi, pre-set |
| | | |
| | 07- | AC / Heat |
| 1 | STD | HVAC System: High capacity ProAir, brushless free blow combination Heat-AC system with digital thermostat control on the action area wall. HVAC unit is mounted in bulkhead at the top of the ALS. |
| 1 | 99-2067 MODIFIED | Thermostat: ProAir dual digital thermostats. Install 2nd digital thermostat to control temperature/fan speed in the Cab Console. ProAir PN: 52-000-726 NOTE: For use with ProAir systems only. NOTE: Locate on Front Console as per prints in special option above. |
| | | |
| | 08- | Cabinets, Hardware & Miscellaneous Items |
| 1 | STD | Main Streetside Wall Cabinets: Specify desired configuration- |
| 1 | OPT | Cabinet Configuration- CPR Seat w/EVS V-4 seat belt system |
| | | Main Wall Cabinets will have (1) adjustable shelf in each and sliding polycarbonate doors with full height extruded handles. See Prints for Configuration. |
| 1 | STD | Action Area Overhead Cabinet: Single cabinet full-height/full-depth of Action Area with sliding polycarbonate doors and full height extruded handles. |
| 1 | NEW DB STD | Action Area shelf to be a non-porous solid surface material. Primary Color: Gray Mist HL-027 Accent Color: Eclipse HL-039 |
| 1 | STD | Action Area and Switch Panel: Laminated, sealed countertop and vertical aluminum panel with SSCOR Suction system collection canister w/SSCOR gauge and quick-connect, (2) Oxygen outlets, (1) 12VDC/USB Outlet, (1) 125VAC Outlet and digital Thermostat. Switch panel includes (10) switch positions and digital clock w/Mode Buttons. |
| 1 | STD | Bulkhead Wall Cabinet: Cabinet above Tech Seat- Electrical Cabinet located over pass-through w/latching, vented door. |
| 1 | NEW DB STD | Vertical Glove Storage Box for (3) Gloves, oriented horizontally, but stacked vertically, with steel door with magentic catch. Located on rear of main wall inside rear entry doors. |

| | | |
|---|---------------|---|
| 1 | NEW DB STD | Locking Drug Box, with right hinged door and Round Southco locking latch, at top of rear cabinet wall inside rear entry doors, above glove box. |
| 1 | STD | ALS Cabinet: Lower section- Locking storage for 747 box, Middle Section- General storage with hinged, 1/2" acrylic doors, (1) non-locking two-point pinch latch on each doors and (1) adjustable shelf. NOTE: Inside access at lower section only. |
| 1 | NEW DB STD | Head of Bench Workstation with Corian Countertop (same color as call-out for Action Area countertop), Backer plate for future monitor install and Single Pull out Aluminum Drawer with Non-Locking Defender Latch, facing the squad bench. Includes notch in cabinet below drawer for additional squad bench length. |
| 1 | Modified | Squad Bench- Reduced Length: (Box out around compt. #6 inside bench) |
| | 1 | Reduced length hinged lid w/TriMark latch for access to interior storage |
| | 2 | Reduced length upholstered seat cushion except over Sharps/Waste Area; formed upholstered back rest cushions and head pad for single seated position. |
| | 3 | (1) EVS V-4 Belted seating position w/progressive foam back and head pad (2nd patient restraints on bench are N/A with this design) |
| 1 | STD | Sharps/Waste: Drop-in style w/Red powder coated hinged lid with standard containers, located at head of squad bench, accessed below workstation counter. |
| 1 | NEW DB STD | Rear Squad Bench Storage/Drawer System. A Pair of Dual Acrylic Dors with Two Round Southco locking latches on each door, and two adjustable shelves to be located at the back of the Squad Bench wall, facing the bench. There will be two aluminum pull out drawers with non-locking Defender latches below the storage cabinet. |
| 1 | STD | Technician's Seat: EVS Rear facing automotive style chair with V-4 belt system mounted on steel base w/side access to storage . |
| 1 | 99-0411 | Seating: EVS Seat Base, EVS CBDL with latching Door- ILOS |
| 1 | STD | Assist Rail, overhead off-center toward Streetside of unit in recessed ceiling panel on Gen-T. |
| 3 | STD | Grab handle- stainless steel, mounted on each rear entry and curbside entry door |
| 7 | STD | Reflective Striping, Door Open Protection: .50" Red reflective striping around interior door pan of all body doors. |
| | | |
| | 09- | Cots & Miscellaneous Items |

| | | |
|-------------|---------|--|
| 1 | 99-0725 | Cot Mount: Stryker Power/Performance Load floor mount plate "Only" installed. ILOS 175-3 LOCATION: Center Mount NOTE: GEN-T DB147 models only |
| | | |
| | 10- | Paint & Lettering |
| 1 | STD | Paint: Body all OEM White |
| | | |
| 0 | DEL | Roof Star ONLY, DELETED |
| | | |
| | | SHIP LOOSE |
| 2 | STD | 5 Lb. Fire Extinguisher- Ship Loose is Standard |
| | | |
| TOTAL ORDER | | |

I have reviewed this Order and find it to be acceptable and ready to build.

Dealer Signature

Date: _____

I have reviewed this Order and find it to be acceptable and ready to build with the addition of the attached, approved changes.

Dealer Signature

Date: _____

Due to on-going product improvements and the changing requirements of the ambulance industry, Gen-T Specialty Vehicles, Inc. reserves the right to change product specifications and related products without prior notice and without any obligation to change prior products or parts. ALL PATENTS RIGHTS RESERVED.