



# Shop Order

Braun Factory Demo  
 Chad Brown  
 1170 Production Drive  
 Van Wert, OH 45891  
 419-232-7020  
 419-232-7070  
 chadb@braunambulances.com

Braun Factory Demo  
 Chad Brown  
 1170 Production Drive  
 Van Wert, OH 45891  
 419-232-7020  
 419-232-7070  
 chadb@braunambulances.com

Rev. Date: 12/22/2010

12/23/2010 Sales Released

Quote No: 10249-0004 / Job/Order No: 5542

FUNCTION 1	PART NO	S	QTY	DESCRIPTION
81255	00-01-0002		1	== Liberty Basic Type I - 2011 / 156" Modu - 10.900 09/17/1
473200(-1)			1	<b>GENERAL VEHICLE INFORMATION</b>
05542-473200				Model Year: 2011      Module Model: Liberty I
				Electrical System: MasterTech
				General Chassis Information:
				Chassis Year: 2011      Chassis Model: Dodge D-5500
				Wheelbase: 168.5"      Chassis Custom Quoted? - Assign
				chassis from canceled Atl. Children's
				Required Delivery Date - FDIC - March 2011
	00-01-0052		1	<b>YES REQUIRED DELIVERY DATE</b>
				This unit must be delivered by this date: FDIC - March 2011
	00-01-0118	S	1	<b>TYPE I - AMBULANCE - D5500 - 72" INTERIOR HEADROOM</b>
				2011 constructed per dimensions and option items as depicted within the attached order line drawings.
80812(-1)	10-04-0003	S	1	<b>CHASSIS - DODGE RAM 5500 168" WB 4x2</b>
05532-1 (+1)				2011
			1	<b>CHASSIS CONVERSION</b>
	20-10-0104		1	<b>AIR SUSPENSION - KELDERMAN</b>
				2011 Standard - Air Ride System - (Kelderman)

FUNCTION 1	PART NO	S	QTY	DESCRIPTION
			1	ELECTRICAL SYSTEM FEATURES
	20-10-0403	1	1	<b>CONDENSER AUXILIARY - MODULE FRONT</b> Auxiliary air conditioning condenser installed on module front IATS (the condenser and wedge mounting brackets painted to match module), per dwg. # 1. (2011 standard)
	50-60-0652	1	1	<b>OXYGEN SYSTEM, MANUAL SYSTEM - MULTIPLEX ELECTRIC</b> Delete electric oxygen - delete bypass (2011 standard)
	30-10-0070	1	1	<b>** NO REAR VIEW / PATIENT AREA VIEW - CAMERA REQUIRED **</b> Deleted as 2011 Standard.
	30-10-0289	1	1	<b>** NO LIGHT ATTENDANT CONTROL PANEL REQUIRED **</b> Deleted as a 2011 Standard.
	30-10-0721	1	1	<b>RECEPTACLE SHORELINE INLET-20 AMP, NON-AUTO EJECT</b> Install 20 amp manual (non-auto eject) shoreline receptacle, per dwg. # 3 (2011 std.)
			1	LIGHTING - FRONT EXTERIOR
	30-25-4104	1	1	<b>LIGHTS, FRONT MODULE WARNING -WHELEN (2)900 HALO/(1)700 HALO</b> Two (2) Whelen 900 series halogen warning lights with red lenses and chrome bezels shall be installed on the module front outer corners. A Whelen 700 series halogen clear light with a chrome bezel shall be installed centered on the front of the module, per dwg # 1. (2011 Standard)
	30-25-0103	1	1	<b>LIGHTS, ICC / LED CLEARANCE - WITH CHROME BEZELS ON FRONT</b> The vehicle shall have five (5) amber surface mounted LED clearance / ICC lights with chrome bezels on the front of the module near the roof line, per dwg. # 1 (2011 standard).
			1	LIGHTING - REAR EXTERIOR
	30-25-0104	1	1	<b>LIGHTS, ICC / LED CLEARANCE - WITH CHROME BEZELS ON REAR</b> The vehicle shall have five (5) red surface mounted LED clearance / ICC lights with chrome bezels on the rear of the module near the roof line, per dwg. # 2 (2011 standard)
	30-26-3001	1	1	<b>LIGHTS, REAR TAIL - WHELEN 600 STOP, TURN &amp; BACK-UP</b> One (1) pair each of Whelen 600 series incandescent stop/tail lights, turn lights, and halogen back-up lights with chrome bezels shall be installed on the rear of the module, per dwg. # 2. (2011 Standard).
	30-26-5002	1	1	<b>** NO REAR WINDOW LEVEL LIGHTS REQUIRED **</b> Deleted as 2011 standard.

FUNCTION 1	PART NO	S	QTY	DESCRIPTION
	30-26-6009	1	1	<b>LIGHTS, REAR MODULE WARNING-WHELEN (5) 900 HALOGEN &amp; SCENE</b> Two (2) Whelen 900 series red halogen warning lights, two (2) Whelen 900 series halogen scene/load lights, and one (1) Whelen 900 series amber halogen warning light shall be installed on the rear of the module. The lights shall be installed with chrome bezels and shall be operated from switches on the master control console labeled "Flashers" and "Rear Scene Lights", per dwg. # 2. (2011 standard)
	30-27-3003	1	1	LIGHTING - SIDE EXTERIOR <b>LIGHTS, SIDE MODULE WARNING - WHELEN 900 HALOGEN - RED</b> Four (4) Whelen 900 series halogen warning lights with red lenses & chrome bezels shall be installed, outboard of the side scene lights - 2011 standard.
	30-27-4101	1	1	<b>** NO REAR INTERSECTION LIGHTS REQUIRED **</b> Deleted - 2011 standard
	50-60-0037	1	1	MODULE FEATURES / EXTERIOR <b>ASSIST HANDLES, (6) BLACK RUBBER</b> A total of six (6) 10-7/8" black vulcanized rubber with steel core assist handles: one (1) handle on each rear door, one (1) on the curbside door, one (1) at the curbside doorway and two (2) at the rear doorway, per dwgs. per dwg. # 5, 6, 7, & 8. 2011 standard.
	40-10-0190	1	1	<b>LOCKS, MANUAL</b> The module passage and compartment doors shall have manual locking devices installed. All module doors shall be keyed alike. (2011 standard).
	50-20-0507	1	1	<b>PASS THROUGH - CAB TO MODULE</b> A window opening shall be provided in the rear of the cab to accommodate pass-through communications to the patient compartment. A bellows shall be provided to connect the cab to the module, per dwg. # 7. (2011 standard).
	40-10-0400	1	1	<b>** NO CURBSIDE WINDOW REQUIRED **</b> Deleted as 2011 standard
	50-60-0391	1	1	<b>HEADLINER - REAR PATIENT COMPARTMENT</b> The headliner in the patient compartment shall be one-piece, seamless, .090 thick aluminum finished withsprayed-on multi-use polychromatic coating. 2011 standard.
	40-10-0302	1	1	<b>STEP ELECTRIC, AUTOMATIC STROMBERG CARLSON AT CURB DOOR</b> Stromberg-Carlson - automatic, electric step curbside doorway IATS Include a cover and mud flaps for protection. (Liberty I standard).

FUNCTION 1	PART NO	S	QTY	DESCRIPTION
			1	MODULE INTERIOR / PATIENT COMPARTMENT FEATURES
	50-01-0402		1	<b>LATCHES CABINET- BLACK</b> All interior hinged cabinet doors and drawers shall be secured with black locking lever latches, per dwgs. (2011 standard).
	50-10-0115		1	<b>CABINET - LEFT WALL, UPPER REAR #1 - FIXED FRAME</b> Delete restocking frame as 2011 standard.
	50-10-0205		1	<b>CABINET - LEFT WALL, UPPER OVER PANEL #2 - FIXED FRAME</b> Delete restocking frames as 2011 standard
	50-10-0307		1	<b>CABINET - LEFT WALL, UPPER FRONT #3 -HINGED DOOR COMPARTMENT</b> The left wall, upper front interior cabinet (#3) shall have a door opening of 17.75" high x 13.25" wide with interior dimensions of 19.00" high x 13.25" wide x 17.25" deep. This compartment shall be enclosed by one (1) hinged acrylic door. The compartment shall be equipped with one (1) adjustable shelf and secured with a latch, per dwg. # 5. (2011 standard)
	50-10-0407		1	<b>CABINET - LEFT WALL, LOWER REAR #4 - FIXED FRAME</b> Delete restocking frame as 2011 standard.
	50-10-0514		1	<b>CABINET - LEFT WALL, LOWER UNDER SECOND ACTION AREA #5</b> The left wall, lower cabinet (#5) under the second action area shall have a door opening of 17.00" high x 13.25" wide with interior dimensions of 18.00" high x 18.00" wide x 17.25" deep. This compartment shall be enclosed by one (1) hinged acrylic door secured with a latch and shall have one (1) adjustable shelf, per dwg. # 5. (2011 standard).
	50-60-0015		1	<b>ASPIRATOR / SUCTION - IMPACT# 324 - SELF CONTAINED - COUNTER</b> An Impact #324 suction system with built-in pump shall be installed on the action wall counter near the attendant's seat, per dwg. # 5 (2011 standard).
	50-60-0340		1	<b>GRAB RAIL, 1-1/4" DIAMETER, (96") OVER COT AREA</b> One grab rail, per dwg. # 9 (2011 standard)
	50-60-0434		1	<b>I V HANGERS, DUAL CEILING, W/ VELCRO STRAPS - PERKO #1309</b> Perko IV hangers, per dwg. # 5 & # 6. (2011 standard)
	50-01-0299		1	<b>** NO INVENTORY CONTROL SYSTEM ON CABINETS REQUIRED **</b> Deleted as 2011 standard.
	50-60-0679		1	<b>** NO SPEAKERS REQUIRED STREETSIDE **</b> Deleted as 2011 standard

FUNCTION 1	PART NO	S	QTY	DESCRIPTION
	50-60-0588		1	<b>** NO SQUAD BENCH RETENTION REQUIRED (NET/ A-BAR) **</b> Deleted as 2011 standard
	50-20-0358		1	<b>** NO CABINET FOR PORTABLE O2 TANK STORAGE REQUIRED **</b> Deleted as 2011 standard.
	50-60-0319		1	<b>** NO GLOVE DISPENSER REQUIRED **</b> Deleted as 2011 standard
	50-60-0091		1	<b>** NO CLOCK REQUIRED **</b> Deleted as 2011 standard
	50-01-0111		1	<b>CABINET CONSTRUCTION - INTERIOR - ALUMINUM</b> All interior cabinets shall be constructed of .090" thick welded aluminum. Wood products shall not be used in the construction of any interior cabinet. All cabinet exteriors, interiors, drawer fronts, drawer interiors, and aluminum doors shall be sealed with a washable sprayed-on multi-use polychromatic coating.(2011 standard).
	50-01-0201		1	<b>CABINET DOORS - CLEAR ACRYLIC</b> Clear (2011 standard)
	50-05-0111		1	CABINETS/ WALLS - POLYCHROMATIC COATING - CAMILLE WHITE Headliner, walls, cabinet faces, and cabinet interiors Zolatone color to be Camille White
	50-10-0919		1	<b>COUNTER TOP - RECESSED ALUMINUM - POLYCHROMATIC SPRAY COATED</b> Recessed counter top with Zolatone color to be Camille White (2011 std.)
	50-60-0840		1	UPHOLSTERY - SPRADLING "ARCTIC" CHARCOAL #9017 All cushions, head pads, door panels and seats shall be covered with Spradling International "Arctic" Charcoal # 9017 expanded vinyl upholstery material.
	50-60-0552		1	<b>LONPLATE II, NON-SLIP EMBOSSED SM. GRID - MICA (GRAY) #421</b> The floor in the patient compartment shall be covered with Lonseal "Lonplate II" non-slip; small grid (embossed) Mica (gray) #421.
	50-60-0153	S	1	<b>COT FASTENER - STRYKER SINGLE - CENTER POS. - NOT INSTALLED</b> Do Not install a Stryker single position center mount until unit is sold.
			1	PAINT / GRAPHICS
	60-01-0002		1	<b>PAINT MODULE - OEM WHITE</b> Paint module OEM white to match the chassis (2011 standard).

PO0036 (-1)