

# EASY GO VAC

ASPIRATOR



## Power & long life on the go in a battery operated suction unit!

### ***It Performs ...***

No need to worry about power when you need it. This high performance unit delivers a vacuum range of 2-21 inHg. The standard easy-to-read gauge allows the care giver to adjust the vacuum.

### ***It Lasts...***

The high performance battery allows 1.5 hours of run time, twice that of comparable units. A "Low Battery Light", standard in this unit, informs the caregiver that the unit needs to be re-charged thus preventing interruptions in use.

### ***It's Convenient ...***

No need to buy a special canister. The Easy Go Vac uses any standard 800 cc canister and is visible in the Carry Bag while unit is in operation. It is re-chargeable in its convenient, specially designed Carry Bag, which also stores the charger, Suction Tubing and optional Auto DC Power Cord.

### ***It's Durable ...***

The ABS plastic cabinet is durable, attractive, easy-to-clean and infection control friendly. There are no open areas on the unit to harbor bacteria and dirt.

### ***It's Protected ...***

A dual pump protection system features two safeguards. A float shut-off in the canister to protect overflow and an Inline Hydrophobic Filter to prevent back flow of fluid as well as airborne contaminants from entering the pump.

### ***It's Dependable ...***

The Easy Go Vac carries a full 2 year warranty on the unit and a 6 month warranty on the battery.





# SPECIFICATIONS

<b>Dimensions (in Carry Bag):</b> Length 12" (30.3 cm), Width 9 1/2" (24.1 cm), Height 10 3/16" (25.9 cm)
<b>Weight (with Carry Bag and all Accessories):</b> 9.6 lbs. (4.4 kg)
<b>Shipping Weight:</b> 11 lbs. (5 kg)
<b>Electrical:</b> Aspirator unit: 12 Volts DC Battery Charger/Power Supply: 100-240 Volts AC
<b>Operating Temperature Range:</b> 50°F to 104°F (10°C to 40°C)
<b>Storage Conditions:</b> Temperature: -4°F to 104°F (-20°C to 40°C); Humidity: Max 95% non-condensing

<b>Vacuum Range:</b> 50 mmHg to 535 mmHg (2 inHg to 21 inHg)
<b>Flow:</b> 14 lpm (unrestricted flow, without suction canister, running on AC power)
<b>Power Consumption:</b> 20 watts
<b>Vacuum Buildup:</b> 0 to 300 mmHg in 3.1 sec. (with 800cc Suction Canister and AC Power Cord connected) 0 to 300 mmHg in 3.5 sec. (with 800cc Suction Canister connected and running on Battery)
<b>Suction Canister:</b> 800cc Disposable with Float Shut-off

# ORDERING INFORMATION

Part#	Description
PM65HG	Easy Go Vac Aspirator (includes all items in Ordering Information except Auto DC Power Cord)
1955	Patient Suction Tubing (6ft.)
502519-10	Canister, 800cc (10 pack)
502956	Carry Bag

Part#	Description
502954	Auto DC Power Cord (optional)
503106	AC Hospital Grade Power Cord
503293	Filter Assembly (Filter, Tubing and Elbow)
503974	Battery Charger/Power Supply



ISO 9001  
Certified

Precision Medical, Inc.  
300 Held Drive • Northampton, PA 18067  
Phone: 610-262-6090 Toll-Free Phone: 1-800-272-7285  
Fax: 610-262-6080 Toll-Free Fax: 1-800-352-1240  
Visit us on the Web: [www.precisionmedical.com](http://www.precisionmedical.com)